

## Remote Control System

### G4 Mini Linear 4 PWM AMP-JPT



A complete remote control system solution using the PCU Mini Economy with linear levers suited for a 4, 5 or 6 section directional control valve using a PWM solenoid with AMP-JPT connectors

#### Scope of delivery

| Item no. | Description                              |
|----------|--|
| 1        | G4 Portable Control Unit MINI Linear-4   |
| 1        | G4 Central Unit                          |
| 1        | G4 Standard supply cable kit             |
| 1        | Standard valve cable kit 1-6 A/B AMP-JPT |
| 1        | Standard battery charger                 |
| 2        | Standard battery pack                    |
| 1        | Standard carrying strap                  |
| 1        | Emergency stop box                       |
| 1        | Pairing plug                             |
| 1        | Instruction manual RC400 G4              |

#### Quick system description

- 12 or 24 V DC Supply voltage
- Portable Control Unit equipped with 4 linear levers for control of 4 (+2) bi-directional analogue functions
- Function shift button allowing additional 2 bi-directional analogue functions as well as 6 digital functions using the 4 push buttons.
- Radio communication at 434 or 900 MHz (ISM-band) using frequency jumping technology
- All analogue functions programmable for final adjustment of speeds
- Complete cable kits for simple installation of supply, digital functions, dump valve and analogue functions
- Standard accessories included such as batteries, battery charger, neck strap and emergency stop button. See below for full system consistency

#### Order information

| Radio / Region | Supply voltage | PWM outputs            | Order reference |
|----------------|----------------|------------------------|-----------------|
| EUROPE         | 24 V DC        | 250 – 640 mA (100 Hz)  | 69108           |
| EUROPE         | 12 V DC        | 500 – 1200 mA (100 Hz) | 44875OU1142     |
| NAFTA          | 24 V DC        | 250 – 640 mA (100 Hz)  | 69107           |
| NAFTA          | 12 V DC        | 500 – 1200 mA (100 Hz) | 44875OU1144     |

## Note

The information in this brochure relates to the operating conditions and applications described.

For applications or operating conditions not described, please contact the relevant technical department. Subject to technical modifications.



**Nordhydraulic**

HYDAC INTERNATIONAL

**Head Office  
HYDAC INTERNATIONAL  
GMBH**

Industriegebiet  
66380 Sulzbach/Saar  
Germany

Tel.: +49 6897 509-01  
Fax: +49 6897 509-577

E-mail: [mobilevalves@hydac.com](mailto:mobilevalves@hydac.com)  
Internet: [www.hydac.com](http://www.hydac.com)