

Accessories for Service Instruments

Aluminium case

for HMG 30X0 and accessories

Part No.: 6042959



Bag with carrying strap

for HMG 30X0

Part No.: 909795



Power supply unit

for HMG 30X0, Spare Part

Part No.: 6054296



ZBE 31

Car charger for HMG 30X0

Part No.: 909739



ZBE 34

Adapter for HMG 30X0 for connecting
HYDAC transmitters

(4 .. 20 mA, 2 conductor)

Male M12x1 to

Binder series 714 M18

(electrical connection type "4")

Part No.: 3236597



ZBE 35

Adapter for HMG 30X0 for connecting
HYDAC transmitters

(4 .. 20 mA, 2 conductor)

Male M12x1 to

Male EN175301-803

(DIN 43650)

(electrical connection type "5")

Part No.: 3236601



ZBE 36

Adapter for HMG 30X0 for connecting an AquaSensor AS 1000

Part No.: 909737



ZBE 38

Y adapter (black) for HMG 30X0 to double the number of input sockets


Part No.: 3224436



ZBE 41

Y adapter (yellow) for HMG 30X0 for connecting a ContaminationSensor CS 1000

Part No.: 910000



ZBE 3010

CAN adapter for HMG 3010 for connecting a CAN-Bus

Part No.: 921238



Connection cable

for HMG 30X0 - PC (USB), Spare Part

Part No.: 6040585



Hydraulic adapter kit

for HMG

2 pieces each

- Adapter hose DN 2 -1620 / 1620 (400 mm and 1000 mm)
- Pressure gauge conn. 1620 / G1/4
- Adapter 1650 / 1620
- Bulkhead union 1620 / 1620

Part No.: 903083



HDS 1000 RPM probe

for HMG 30X0

including reflective foil set

Part No.: 909436

HDS 1000 reflective foil set

Spare Part, Quantity: 25

Part No.: 904812



UVM 30X0

Module for HMG 30X0 for connecting different input signals

Part No.: 909752



Plastic case

for HMG 500/510 and accessories

Part No.: 6043006



Power supply (230 V AC)

for HMG 500/510

Part No.: 6043562



Connection cable

for HMG 510 - PC (USB), Spare Part

Part No.: 6049553



ZBE 30-02 (5 pole)

Connection cable M12x1, 2 m male/female

Part No.: 6040851

ZBE 30-05 (5 pole)

Connection cable M12x1, 5 m male/female

Part No.: 6040852



SSH 1000

Sensor simulator to simulate 2 HSI sensors, ideal for training purposes

Part No.: 909414



Note:

The information in this brochure relates to the operating conditions and applications described.

For applications or operating conditions not described, please contact the relevant technical department.

Subject to technical modifications.

HYDAC ELECTRONIC GMBH

Hauptstraße 27, D-66128 Saarbrücken

Telephone +49 (0)6897 509-01

Fax +49 (0)6897 509-1726

E-mail: electronic@hydac.com

Internet: www.hydac.com