



HYDAC Fluid Technology Compact Power Units Overview AC / DC



EMDAD INTERNATIONAL



DCM

DC1

CO1

CO2

CO3

CA2

HP

ML

HYDAC Compact Power Units

For over 25 years, HYDAC Fluidtechnik has been building compact power units which in these changing times have remained at the cutting edge of technological development. They are noted generally for their compact installation dimensions and high power density. Starting from 0.32 l/min, there are many different models to provide tailor-made solutions for the customer.

	bar 100 200	300 400	500	l/min 5 10 15 20 25 30
^ع .	Up to 250 bar Short-time duty Intermittent duty	up to 5.6 l/min S2 = starting at 1 S3 = starting at 3	min*	DC power units for controlling tail-lifts and other robust mobile applications. Can be installed in three positions – particularly splashproof
	bar 100 200 Up to 250 bar Short-time duty Intermittent duty	★300 400 1 up to 18.4 I/min S2 = starting at 1.8 S3 = starting at 4		Vmin 5 10 15 20 25 30 DC power units for controlling tail-lifts, storage and retrieval machines, working platforms, forklifts etc
*	bar 100 200 Up to 250 bar Short-time duty Intermittent duty	3001 400 1 up to 20 l/min S2 = 5 min* S3 = 20 %*	500	Imin 5 10 15 20 25 30 Power unit with low installation height and transparent oil tank (steel tank available a an option). For scissor-lift platforms, dock levellers, machine tools, wind turbines, vehicle hoists
*	bar100 200 Up to 250 bar Short-time duty Intermittent duty Continuous-opera periodic duty	3001 400 1 up to 20 l/min S2 = 5 min* S3 = 25 %* tion** S6 = 25 %*	500	Imin 5 10 15 201 251 30 AC power unit with steel tank for more robust applications, e.g. energy technology, points switching, machine tools (**with cooler module)
*	bar100 200 Up to 250 bar Short-time duty Intermittent duty Continuous-opera periodic duty	3001 400 1 up to 30 l/min S2 = 10 min* S3 = 30 %* tion S6 = 30 %*	500	Vmin5 10 15 201 251 30 Modular power units in AC or 3-phase design with oil conditioning concept and energy-efficient single or double pump une.g. for lathes, machine tools
*	bar 100 200 Up to 250 bar Short-time duty Intermittent duty	400 up to 12.6 l/min S2 = 3 min* S3 = 10 %*	500	Vmin5 10 15 20 25 30 Power unit concept with oil-immersed motorpump unit. Particularly suitable for outdoor use, e.g. in traffic barriers, dock levellers, for points switching
<u></u>	bar100 200 Up to 500 bar Short-time duty Intermittent duty	3001 400 1 up to 5.25 l/min S2 = 3 min* S3 = 10 %*	500	Imin5 10 15 201 251 30 High-pressure hydraulics in the most compact space. Three-phase power unit, e.g. for clamping of forming tools, brake calliper operation
	bar100 200 Up to 500 bar	300 400 400 400 400 400 400 400 400 400	500	I/min5 10 15 20 25 30 Modular valve stacking system for high pressure hydraulics. For expansion of the control functions of HP compact power units.
	bar100 200 Up to 350 bar	3001 400 1 up to 20 I/min	500	I/min 5 10 15 20 25 30 Modular valve stacking system. Simple expansion (also as retrofit) of control functions for compact power units.

E 5.311.0 /09.13

1



Up to 250 bar Up to 5.6 l/min Short-time duty S2 = from 1 min* Intermittent duty S3 = starting at 3 %*

HYDAC Compact Power Units with DC Motor DC Mobile

GENERAL

- Maximum protection against salt and spray through the use of specially formed plastic parts such as tank and cowl
- Reduction in noise emissions achieved with vibration-resistant plastic casing
- Can be installed in 3 different positions without having to undertake any modifications
- Outputs of 1.2 to 2.2 kW in 12 and 24 Volt DC, and 3 different tank sizes are possible due to modular design



SPECIFICATIONS	
Flow rate:	2.5 to 5.6 l/min
Operating pressure:	max. 200 bar
Peak pressure:	up to max. 250 bar
Duty cycle:	S2 (short-time duty)
Motor:	Pn = 1.2 kW 2.2 kW
Motor voltages:	12 and 24 Volt
Protection class:	DIN EN 60034-5 min IP 54
Pump displacement:	0.8 cm ³ /rev 2.6 cm ³ /rev
Tank volume:	4.0 7.5
Useable volume:	2.2 - 6.3
Operating fluid:	Hydraulic oil to DIN 51524 Part 1 and 2
Temperature range of operating fluid:	-20°C to max. +80°C
Ambient temperature range:	-20°C to max. +40°C
Viscosity range:	10 – 380 mm²/s is recommended
Filtration:	Class 21/19/16 to ISO 4406 or cleaner
Cooling:	Convection cooling
Weight:	from 9 to 12 kg
Return flow rate:	up to max. 20 I/min
Installation position:	Vertical, horizontal, horizontal on side
Further details in Brochure No. 5.309.0	

N E 5.311.0 /09.13



Up to 250 bar Up to 18.4 I/min Short-time duty S2 = starting at 1.5 min* Intermittent duty S3 = starting at 4%*

HYDAC Compact Power Units with DC Motor DC1

- Space-saving design due to small flange
- Very low noise levels due to special construction
- Possible to have different hydraulic controls in the same flange due to flexible configuration of cartridge valves and / or by fitting control blocks and standard function modules



Flow rate:	up to 18.4 I/min
Operating pressure:	max. 250 bar
Peak pressure:	up to max. 300 bar (on request)
Duty cycle:	S2 (short-time duty)
	S3 (intermittent duty)
Motor:	Pn = 1.7 kW 3.0 kW
Motor voltages:	12 and 24 Volt
Protection class:	DIN EN 60034-5 min IP 54
Pump displacement:	1.0 cm ³ /rev 8.0 cm ³ /rev
Tank volume:	1.8 - 8.4
Useable volume:	1.2 - 7.8
Operating fluid:	Hydraulic oil to DIN 51524 Part 1 and 2
Temperature range of operating fluid:	-20°C to max. +80°C
Ambient temperature range:	-20°C to max. +40°C
Viscosity range:	10 - 380 mm ² /s is recommended
Filtration:	Class 21/19/16 to ISO 4406 or cleaner
Cooling:	Convection cooling
Weight:	from 15 to 25 kg
Return flow rate:	up to max. 40 l/min
Installation position:	Vertical, horizontal



Up to 250 bar Up to 20 l/min Short-time duty Intermittent duty

S2 = 5 min* S3 = 20%*

HYDAC Compact Power Units with 3-Phase Motor CO1

GENERAL

- Space-saving design due to small flange
- Possible to have different hydraulic controls in the same flange due to flexible configuration of cartridge valves and / or by fitting control blocks and standard function modules
- Very low noise levels due to special construction



Flow rate:	up to 20 I/min		
Operating pressure:	max. 250 bar		
Peak pressure:	up to max. 300 bar (on request)		
Duty cycle:	S2 (short-time duty)		
	S3 (intermittent duty)		
Motor:	Pn = 0.37 kW 3.0 KW (4; 5.5 KW upon request		
Motor voltages:	3 Ph. 230/400V -50 Hz (others on request)		
Protection class:	DIN EN 60034-5 min IP 54		
Pump displacement:	1.0 cm ³ /rev 10.0 cm ³ /rev		
Tank volume:	1.8 – 8.4 I		
Useable volume:	1.2 – 7.8		
Operating fluid:	Hydraulic oil to DIN 51524 Part 1 and 2		
Temperature range of operating fluid:	-20°C to max. +80°C		
Ambient temperature range:	-20°C to max. +40°C		
Viscosity range:	10 – 380 mm ² /s is recommended		
Filtration:	Class 21/19/16 to ISO 4406 or cleaner		
Cooling:	Convection or air cooling		
Weight:	from 12 to 20 kg		
Return flow rate:	up to max. 40 l/min		
Installation position:	Vertical, horizontal		

E 5.311.0 /09.13

4


JAP INTERNATIONAL



Up to 250 bar Up to 20 l/min Short-time duty S2 = 5 min* Intermittent duty S3 = 25%* **Continuous-operation** periodic duty S6 = 25 %* (with cooler module)

HYDAC Compact Power Units with 3-Phase Motor CO2

- Compact and lightweight power packs achieved through the use of progressive motors and aluminium flanges
- Robust version through the use of metal tank •
- Wide variety of controls using standard function modules •
- Easy to maintain as control valves are easily accessible •
- Low-noise version •



Flow rate:	up to 20 l/min
Operating pressure:	max. 250 bar
Peak pressure:	up to max. 300 bar (on request)
Duty cycle:	S2 (short-time duty)
	S3 (intermittent duty)
	S6 (continuous-operation periodic duty)
Motor:	Pn = 0.37 kW 5.5 kW
Motor voltages:	3 Ph. 230/400V -50 Hz (others on request)
Protection class:	DIN EN 60034-5 min IP 54
Pump displacement:	1.0 cm ³ /rev 10.0 cm ³ /rev
Tank volume:	2.5 – 16.6 I (steel tank, square: 19 I)
Useable volume:	2.0 – 14.5 l
Operating fluid:	Hydraulic oil to DIN 51524 Part 1 and 2
Temperature range of operating fluid:	-20°C to max. +80°C
Ambient temperature range:	-20°C to max. +40°C
Viscosity range:	10 – 380 mm²/s is recommended
Filtration:	Class 21/19/16 to ISO 4406 or cleaner
Cooling:	Convection or air cooling
Weight:	from 12 to 20 kg
Return flow rate:	up to max. 40 l/min
Installation position:	Vertical, horizontal

INTERNATIONAL



Up to 250 bar Up to 30 l/min Short-time duty Intermittent duty **Continuous-operation** periodic duty

S2 = 10 min* S3 = 30%*

S6 = 30 %*


HYDAC Compact Power Units with AC or 3-Phase Motor CO3

- Actuation of consumers made flexible by optional combination of double pump (energy efficiency)
- Robust aluminium oil tank with volume of 20 to 70 litres
- Low-noise motor
- High duty cycle possible



e duty)
nt duty)
s-operation periodic duty)
V -50 Hz (others on request)
-5 min IP 54
(up to 32 ccm ³ on request)
also possible
DI
BI
to DIN 51524 Part 1 + Part 2
+80°C
+40°C
s is recommended
6 to ISO 4406 or cleaner
ooler
kg
I/min
ontal
C

<u>EMDAD</u> INTERNATIONAL



Up to 250 bar Up to 12.6 l/min Short-time duty Intermittent duty


S2 = 3 min* S3 = 10%*

HYDAC Compact Power Units with Oil-Immersed Motor/Pump Unit CA

- Very compact and low-noise as motor-pump unit is oil-immersed in the tank
- High leakage resistance and stability due to deep-drawn steel tank
- Space-saving design due to small flange
- Standard terminal board on the front face simplifies electrical installation
- High performance compact units



SPECIFICATIONS	4.2 to 42.0 l/min
Flow rate:	1.3 to 12.6 l/min
Operating pressure:	max. 250 bar
Duty cycle:	S2 (short-time duty)
	S3 (intermittent duty)
Motor:	Pn = 0.55 kW 3.0 kW
Motor voltages:	3 Ph. 230/400V -50 Hz (others on request)
Protection class:	DIN EN 60034-5 min IP 54
Pump displacement:	1.0 cm³/rev 4.75 cm³/rev
Tank volume:	5.0 - 9.0
Useable volume:	2.5 - 7.3
Operating fluid:	Hydraulic oil to DIN 51524 Part 1 and 2
Temperature range of operating fluid:	
Ambient temperature range:	-20°C to max. +40°C
Viscosity range:	10 – 380 mm ² /s is recommended
Filtration:	Class 21/19/16 to ISO 4406 or cleaner
Cooling:	Convection cooling
Weight:	from 12 to 24 kg
Return flow rate:	up to max. 25 l/min
Installation position:	Vertical, horizontal



Up to 500 bar Up to 5.25 l/min Short-time duty Intermittent duty

S2 = 3 min* S3 = 10%*


HYDAC Compact Power Units High Pressure Power Unit with 3-Phase Motor HP

- High power density and simultaneously compact construction
- Position of terminal box in the top of the unit simplifies electrical installation
- Radial piston pump is oil-immersed in the sturdy tank
- Very low noise emissions due to noise-damping cast-iron housing
- Wide range of build-on controls available



Flow rate:	0.3 to 5.25 l/min
Operating pressure:	max. 500 bar
Duty cycle:	S2 (short-time duty)
	S3 (intermittent duty)
Motor:	Pn = 1.2 kW 2.2 kW
Voltages:	3 Ph. 230/400V -50 Hz (others on request)
Protection class:	DIN EN 60034-5 min IP 54
Pump displacement:	0.3 cm ³ /rev 5.25 cm ³ /rev
Tank volume:	1.1 - 7.0
Useable volume:	0.7 – 5.8
Operating fluid:	Hydraulic oil to DIN 51524 Part 1 and 2
Temperature range of operating fluid:	-20°C to max. +80°C
Ambient temperature range:	-20°C to max. +40°C
Viscosity range:	10 – 380 mm ² /s is recommended
Filtration:	Class 21/19/16 to ISO 4406 or cleaner
Cooling:	Convection cooling / air cooling
Weight:	from 7.2 to 25.7 kg
Return flow rate:	up to max. 10 l/min
Installation position:	vertical

INTERNATIONAL



Up to 500 bar Up to 12 l/min

HYDAC Valve Stacking System L

- Individually extendable stacking system for controlling low-volume consumers and pressure/load-holding tasks.
- A high level of flexibility for both designers and builders
- Small dimensions combined with high power density •
- No leakage thanks to short, robust connections
- Valve stack can be extended by retrofitting with additional modules



SPECIFICATIONS	
Flow rate:	up to 12 l/min
Operating pressure:	max. 500 bar
Voltages:	24 and 230 volts
Protection class:	DIN EN 60034-5 min IP 65
Operating fluid:	Hydraulic oil to DIN 51524 Part 1 and 2
Temperature range of operating fluid:	-20°C to max. +80°C
Ambient temperature range:	-20°C to max. +40°C
Viscosity range:	10 – 380 mm ² /s is recommended
Filtration:	Class 21/19/16 to ISO 4406 or cleaner
Weight:	from 0.2 to 2.2 kg per individual module
Return flow rate:	up to max. 15 l/min
Can be flange-mounted to:	CO1, DC1, CA and HP power units
Further details can be found in Brochu	ure No. 5.304.2



Up to 350 bar Up to 20 l/min

HYDAC Valve Stacking System ML

- Individually extendable stacking system with integrated installation and sealing elements.
- A high level of flexibility for both designers and builders
- Small dimensions combined with high power density
- No leakage thanks to short, robust connections
- Valve stack can be extended by retrofitting with additional modules



(See)
12 to 20 I/min
max. 350 bar
24 and 230 volts
DIN EN 60034-5 min IP 65
Hydraulic oil to DIN 51524 Part 1 and 2
-20°C to max. +80°C
-20°C to max. +40°C
10 – 380 mm²/s is recommended
Class 21/19/16 to ISO 4406 or cleaner
from 0.5 to 6.4 kg per individual module
up to max. 20 l/min
CO1, DC1, CA and HP power units
ire No. 5.308.

AD INTERNATIONAL

Information on **Intermittent Duty**




- No leakage thanks to short, robust connections
- Can be extended by retrofitting with additional modules
- With S1, thermal equilibrium is reached: thermal energy supplied = thermal energy dissipated, and in this connection the maximum temperature is 80° C
- Compact power units cannot be operated continuously •

SHORT-TIME DUTY (duty type S2)

- With S2, the operation time on load is not sufficient to reach thermal equilibrium
- Compact power units are designed for short-time operation S2

INTERMITTENT PERIODIC DUTY (duty type S3)

- The cycle time (T b + T st) is so short that thermal equilibrium is not reached
- The cycle time must not exceed 10 minutes
- Compact power units are designed for intermittent periodic operation S3





Ð

 ϑ max

θ max

θmax







*S*1

t

S2

р


19

P


v

MAD INTERNATIONAL

Information on Intermittent Duty



ϑ max θ



CONTINUOUS-OPERATION PERIODIC DUTY (duty type S6)

- The cycle time time with constant load and a rest period (tB + t L) is so • short that thermal equilibrium is not reached
- The cycle time must not exceed 10 minutes
- Some Compact power units are designed for continuous-operation periodic duty S6

CALCULATING A COMPACT POWER UNIT

Calculation example: The relative duty cycle tr is calculated as follows:

$$T_{R} = \frac{T_{B}}{T_{B} + T_{L}} \times 100\%$$
$$- T_{B} = 20 \text{ sec}$$
$$- T_{L} = 80 \text{ sec}$$
$$20$$

 $T_R = \frac{20}{20 + 80} \times 100 \% = 20 \%$