# EN 18.321.3/02.18

# DAC INTERNATIONAL



# **AquaSensor**

AS 1000

Saturation level

**Temperature** 

## **Description:**

The AquaSensor AS 1000 is the culmination of continued development of the successful AS 2000 series for online detection of water in oils, in particular as an OEM sensor for fluid conditioning monitoring. It measures the degree of saturation and the temperature of

In the analogue output version, the AS 1000 transmits the values for the saturation level and the temperature as a 4 .. 20 mA signal.

In the version with two switching outputs, the AS 1000 can be configured by the user via the HYDAC service units HMG 3010 and HMG 4000, the Condition Monitoring Unit CMU 1000 and the interface module CSI-B-2. The following parameters can be adjusted:

- Saturation level / temperature
- Switch points
- Switching mode of switching outputs
- Switching direction
- Switching delay times

The AS 1000 therefore enables hydraulic and lubrication oils to be monitored accurately, continuously and online. As water problems are detected early on, malfunctions and unnecessary downtime can be reliably avoided

# analogue output

2 switching outputs or

#### **Technical data:**


Input data	
Saturation level	0 100 %
Temperature	-25 100 °C
Operating pressure	-0.5 50 bar
Pressure resistance	≤ 630 bar
Mechanical connection	G3/8 A DIN 3852
Tightening torque, recommended	25 Nm
Parts in contact with fluid	Mechanical connection: stainless steel / vacuum-metallised ceramic Seal: FKM or EPDM
Output data	
Pin 2: Saturation level	
Output signal	4 20 mA (corresponds to 0 100 %) R <sub>Lmax</sub> = (U <sub>B</sub> - 10 V) / 20 mA [kW] or switching output (configurable)
Calibration accuracy	≤ ± 2 % FS max.
Accuracy in media measurements	≤ ± 3 % FS typ.
Pressure dependence	± 0.025 % FS / bar
Pin 4: Temperature	
Output signal	4 20 mA (corresponds to -25 +100 °C) R <sub>Lmax</sub> = (U <sub>B</sub> - 10 V) / 20 mA [kW] or switching output (configurable)
Accuracy	≤ ± 2 % FS max.
Pin 5:	HSI (HYDAC Sensor Interface) Automatic sensor recognition
Switching outputs	
Туре	PNP transistor outputs (configurable as N/O or N/C)
Switching current	maximum 1 A per switching output
Environmental conditions	
Compensated temperature range	0 +90 °C
Operating temperature range 1)	-40 +100 °C / -25 +100 °C
Storage temperature range	-40 +100 °C
Fluid temperature range 1)	-40 +125 °C / -25 +125 °C
Viscosity range	
	1 5000 cSt
Flow velocity	< 5 m/s
Flow velocity	< 5 m/s Mineral oil based fluids, synthetic and natural
Flow velocity Fluid compatibility 2)	< 5 m/s Mineral oil based fluids, synthetic and natural esters
Flow velocity Fluid compatibility ²)  C € mark	< 5 m/s Mineral oil based fluids, synthetic and natural esters EN 61000-6-1 / 2 / 3 / 4
Flow velocity Fluid compatibility ²)  C € mark  Protection class acc. to DIN EN 60529 ³)  Other data  Supply voltage	< 5 m/s Mineral oil based fluids, synthetic and natural esters EN 61000-6-1 / 2 / 3 / 4
Flow velocity Fluid compatibility ²)  C € mark  Protection class acc. to DIN EN 60529 ³)  Other data  Supply voltage  Residual ripple of supply voltage	< 5 m/s Mineral oil based fluids, synthetic and natural esters EN 61000-6-1 / 2 / 3 / 4 IP 67
Flow velocity Fluid compatibility <sup>2)</sup> ( € mark  Protection class acc. to DIN EN 60529 <sup>3)</sup> Other data  Supply voltage  Residual ripple of supply voltage  Current consumption	< 5 m/s Mineral oil based fluids, synthetic and natural esters EN 61000-6-1 / 2 / 3 / 4 IP 67 12 32 V DC ≤ 5 % ≤ 30 mA without outputs
Flow velocity Fluid compatibility ²)  C € mark  Protection class acc. to DIN EN 60529 ³)  Other data  Supply voltage  Residual ripple of supply voltage	< 5 m/s Mineral oil based fluids, synthetic and natural esters EN 61000-6-1 / 2 / 3 / 4 IP 67 12 32 V DC ≤ 5 % ≤ 30 mA without outputs ~ 145 g

Note: reverse polarity protection, short circuit protection provided.

FS (Full Scale) = relative to complete measuring range

- 1) -25 °C with FKM seal, -40 °C on request
- 2) Special fluids on request
- 2) With mounted mating connector in corresponding protection class

#### **Dimensions:**



## Model code:

Fluid 1)

AS 1 X 0 8 - X - 000

#### Mechanical connection

= G3/8 A DIN 3852

#### **Electrical connection**

= male M12x1, 5 pole (mating connector not supplied)

= operating fluid mineral oil-based

= operating fluid phosphate ester-based

#### **Output signal**

- = output 1 pin 2 saturation level (4 .. 20 mA) output 2 pin 4 temperature (4 .. 20 mA)
- = 2 switching outputs

#### **Modification number**

000 = standard

#### Note:

1) Special fluids on request

#### Accessories:

Appropriate accessories, such as mating connectors, can be found in the Accessories brochure.

#### Note:

The information in this brochure relates to the operating conditions and applications described. For applications or operating conditions not described, please contact the relevant technical department.


Subject to technical modifications.

## **HYDAC ELECTRONIC GMBH**

Hauptstr. 27, 66128 Saarbrücken Germany Telephone +49 (0)6897 509-01

Fax +49 (0)6897 509-1726 e-mail: electronic@hydac.com Internet: www.hydac.com

#### Pin connections:



Pin	AS 1X08-C	AS 1X08-2
1	+U <sub>B</sub>	+U <sub>B</sub>
2	Saturation level 4 20 mA	SP2
3	0 V	0 V
4	Temperature 4 20 mA	SP1
5	HSI*	HSI*

\* HSI = HYDAC Sensor Interface (HYDAC's own communication interface)

### Display, read-out and configuration options:

#### HDA 5500-1-1-xC-000

Digital Display Unit with 2 programmable switching outputs, specifically designed for use with the AS 1000

HDA 5500-1-1-AC-000 Order no.: 908869 HDA 5500-1-1-DC-000 Order no.: 908870

#### **HMG 510**

Portable 2-channel measuring instrument, specially designed for use with HSI and SMART sensors

Order no.: 909889

#### HMG 3010 and HMG 4000

Portable data recorders with fully graphicscapable colour display for displaying, recording and processing measured values as well as for configuring of HSI and SMART sensors

#### **CMU 1000**

Electronic evaluation unit for online monitoring of measured value as well as for the configuration of HSI and SMART sensors Order no. 920718

#### CSI-B-2

Interface module, enables configuration of HSI and SMART sensors using HYDAC PC software **CMWIN** 

Order no. 920134

Information on other read-out options can be found on our website at www.hydac.com or please contact your HYDAC representative.