



# HYDAC INTERNATIONAL

## Mobile Valves



























### Kits, Electronics, Software







THE **POWER** FLOWS












Universal Standard Directional Control Valves

Valve Types Overview		Open Center Valves						
Product name		RM 230	RM 270	RS 160	RS 210	RS 220	RSQ 240	DX-6
								
Technology		Non-pressure compensated – Open Center (OC) Technology						
Pump types and performance								
	Fixed displacement pump	●	●	●	●	●	●	●
	Variable displacement pump	–	–	●	–	●	●	●
Q <sub>max</sub> Pump [l/min]		70	120	60	70	80	120	180
Q <sub>max</sub> Work port [l/min]		70	120	60	70	80	100	180
p <sub>max</sub> Pump [bar]		210	210	250	350	350	350	350
Valve types (monobloc or sectional)		mono	mono	section	section	section	section	section
Max. number of sections		4	4/6	10	10	10	10	10 (20)
Spool control								
Open spool end for mechanical attachment		●	●	–	●	–	●	●
	Hand lever							
	Pneumatic	●	●	●	●	–	–	●
	Electro-pneumatic ON/OFF	●	●	●	●	–	–	●
	Hydraulic	●	●	●	●	●	●	●
	Electro-hydraulic	–	–	●	–	●	●	●
	CAN Bus (ICU technology*)	–	–	–	–	–	–	●
Port working sections		G ½"	G ¾"	G ¾"	G ½"	G ½"	G ½"	G ¾"
Main applications		   						
* Please contact our technical sales, not available at present								


X-Series

Frontloader Valves	Selector Valves
RMS 202	RV 713
	
Non-pressure compensated	
•	•
•	•
120	80
90	60
250	300
mono	mono
2	1
	6/2
•	–
–	–
–	–
–	–
–	–
•	•
–	–
G ½"	G ¾ – ½"
	

X-Series X-Series

Load Sensing Valves		
HX1	LX-3	LX-6
		
Pressure compensated – Load Sensing (LS) Technology		
•	•	•
•	•	•
120	150	250
70	100	180
250	350	350
section	section	section
10	10	10
–	–	–
–		
–	–	–
–	–	–
•	•	•
•	•	•
–		•
–	•	•
G ½"	G ½"	G ¾"
		

X-Series – Spool Control Options for LX-3, LX-6, DX-6



**Spring Caps**

1 Standard spring cap

2 Spring cap with position indicator HLS 200

3 Spring cap for floating position spool

**Operation Units**

4 Manual control with encapsulated spool ends


5 Hydraulic control (with/without manual override)

6 Electro-hydraulic control (with/without manual override)

7 Electronic control unit (ICU) via CAN-Bus system

### Advanced CAN-Bus Control by ICU (Intelligent Control Unit\*) for X-Series Valve Systems

The Intelligent Control Unit (ICU) ensures the control of a mobile valve spool with spring centered neutral position and advanced control/monitoring options.



**Product Features**

**Motor actuation with**

- High precision
- Quick response
- Hysteresis free
- Contamination resistant (pilot oil-free control)
- Power boost – for higher force in emergency cases

**Ready for the road**

- Easy to customize parameters via HYDAC MATCH
- Auto-Addressing - at initial start-up
- Auto-Calibration – at production end-of-line test
- Auto-Service – import information from neighbor ICU
- Protocol: HYDAC MATCH, J1939, optional CANopen
- With and without manual override

**Intelligent electronics**

- Adjustable valve characteristics and performance
- Spool condition monitoring – position and force
- Intelligent malfunction management – active service

**Optional**

- Integrated pressure and temperature sensors
- I/O's for external analogue sensors /actuators

**CAN**

**MATCH**

\* Please contact our technical sales, not available at present

## The Easy to Implement Plug & Work “Crane Control System” by TECHNION

**xCrane**



Xcrane is a turnkey electronic control system for mobile cranes.

### Product Features

- Fast response times
- Smooth individual controls for each operator
- Truly compatible with both current and voltage controlled valves
- An I/O set enables it to be interfaced with a variety of sensors, joysticks and third party modules

## The Easy to Implement Open Loop “Crane Tip Control System” by TECHNION

**xCrane PLUS**



Xcrane Plus is designed for operators who need both a parallel crane and a traditional forestry crane depending on the work phase. The traditional forestry crane works as a parallel crane just by choosing the parallel mode from the display. In parallel mode the lift boom and the outer boom are operated simultaneously with one joystick control. In this mode the operator can also activate the automatic extension. When this is selected, the control imitates the tip control mode; the lift boom, outer boom and extension are moving at the same time with left-hand joystick movement.

### Product Features

- Enables to drive multiple crane movements simultaneously at the same time with only one joystick movement

## The Advanced Closed Loop “Crane Tip Control System” by TECHNION

**xCrane PRO**



Xcrane Pro controls the tip of the boom instead of controlling each cylinder separately.

### Product Features


- Sensors calculate the cylinder positions for main boom, outer boom and extension
- Algorithms calculate optimal way to move crane tip based on these sensors
- Enables automated movements and collision prevention
- Extremely effective, fast and precise
- Easy to learn and use, ergonomic
- Constant speed of crane tip reduces stress on crane and base machine
- End damping – slows down speed in end positions automatically increasing well-being at work and lifetime of the crane
- Increases significantly ergonomics for the operators
- Quick to implement hardware with “pro” application engineering support for any crane geometry or hydraulic solution

 **TECHNION**  
HYDAC INTERNATIONAL

#### Contact


TECHNION Ltd., Linkkikatu 15, 21100 Naantali, FINLAND  
Phone: +358 40 191 1000  
Email: xCrane@technion.fi





E H C

- Implementation of the four proportional functions that can, for example, be controlled via joystick, through a combination of two controllers in versions BASIC and BASICplus
- With flowsharing technology for continuous movement with parallel control of multiple functions even under maximum pump demand



## MATCH Subsystems

Our electrohydraulic subsystems are developed based on MATCH and are tested comprehensively in all of the available configurations and ranges of functions. In terms of functional safety, we offer solutions up to the safety levels PLd or AgPLd (SRL2).

Our portfolio includes software for electro-hydraulic machine control, for electro-hydraulic auxiliary steering systems, electro-hydraulic additional steering systems and electro-hydraulic or electric fan controls.

We also provide the subsystem configuration tool SCT for the users of the subsystem software. The SCT enables configuration of the functionalities, parametrization and calibration of the software.

A licence is required on the controller to operate the software. This can be managed with the SCT.

## EHC – Software for Electro-hydraulic Machine Control

The software for electro-hydraulic control (EHC) is a machine application software for manual control of mobile valves that are controlled by proportional valves.

The valve spool can be controlled directly by solenoid or pilot-controlled via proportional pressure-reducing valves. The application is available on the controllers HY-TTC 32/HY-TTC 32S – depending on the required level of functional safety.

The EHC software makes it easy to develop a system for machine control: you can apply the signals from analogue joysticks, push-buttons or switches to the controller inputs, combine the current outputs in pairs with pilot valves of the mobile valve axis and then configure the software functionalities to suit the system behaviour you require.

The subsystem configuration tool SCT can be used to commission and service the EHC software. The SCT USER, standard version, is included in delivery.

### Available EHC Versions

The following EHC software variants, which build on each other, are available, with each one working on its own controller HY-TTC 32(S):

#### BASIC

Proportional and/or on/off valve control, with evaluation of a large number of different analogue joystick signals. Your machine can be operated safely in combination with the implemented release functions.

#### BASICplus

BASICplus contains the entire function range of the BASIC version. A continuous hydraulic function is also provided, which provides much greater ease of use thanks to its adjustable and retrievable flow rate adjustment. The electronic flowsharing makes it possible for you to operate a classic load-sensing valve – such as one from the HYDAC LX family – like a valve with downstream pressure compensators.

**See also:** HYDAC Software Product Catalogue EN 18.500.1.0


#### Contact:

##### HYDAC SOFTWARE GmbH

Zum Kiesberg 15–16, 14979 Großbeeren (near Berlin), Germany  
Tel.: +49 33701 3389-4410, E-mail: [info.software@hydac.com](mailto:info.software@hydac.com)



Accumulator Technology 30.000




Filter Technology 70.000



Control Technology 18.500



Filter Systems 79.000



Compact Hydraulics 53.000



Accessories 61.000




Electronics 180.000



Cooling Systems 57.000

**Global Presence.  
Local Expertise.**  
[www.hydac.com](http://www.hydac.com)



- 📍 HYDAC Headquarters
- HYDAC Companies
- HYDAC Sales and Service Partners
- ▲ Free Sales Partners



**Nordhydraulic**  
HYDAC INTERNATIONAL

**Head Office**  
**HYDAC INTERNATIONAL**  
**GMBH**

Industriegebiet  
66280 Sulzbach / Saar  
Germany

Tel.: +49 6897 509-01  
Fax: +49 6897 509-577

E-mail: [mobilevalves@hydac.com](mailto:mobilevalves@hydac.com)  
Internet: [www.hydac.com](http://www.hydac.com)

**Note**

The information in this brochure relates to the operating conditions and applications described. For applications and/or operating conditions not described, please contact the relevant technical department. Subject to technical modifications.