


FUNCTION



The proportional pressure control valve is a direct-acting 3-way spool type valve - with pressure protection on outlet side. When de-energized, connection 2 is closed and consumer port 1 is connected to tank port 3.

When the inlet pressure fluctuates, it provides an almost constant

outlet pressure - depending on the coils' current supply.

When the control current increases, the solenoid pushes on the control piston with a force that is proportional to the control current and thus sets the control pressure at port 1. Pressures at tank port 3 increase the control pressure. If, as a result of external influences, the pressure at port 1 rises above the setting pressure, the valve opens from port 1 to tank port 3 (relief function).

3-way proportional pressure control valve spool valve, direct acting metric cartridge valve – 100 bar PDR10830-01

GENERAL

- For example for large pilot control units and for non-automated clutch applications
- Excellent stability throughout the entire flow range
- Different pressure ranges up to 32 bar available
- Excellent dynamic performance
- Coil seals protect the solenoid system
- Wide variety of connectors available
- External surfaces with advanced corrosion protection due to ZnNi coating (1 000 h salt spray test)

SPECIFICATIONS*

max. 100 bar ((at port 2)	
max. 80 bar (at port 3)		
18; 20; 25 or 3	18; 20; 25 or 32 bar	
max. 40 l/min		
< 100 cm³/min at 18 bar		
	n²/s at average current supply	
	min20°C to max. + 60°C	
Hydraulic oil to	Hydraulic oil to DIN 51524 Part 1, 2 and 3	
	min. 7.4 mm²/s to max. 420 mm²/s	
Class 18/16/13 to ISO 4406 or cleaner		
150 – 1200 years, according to DIN EN ISO 13849-1		
No orientation restrictions		
Valve body:	Steel	
Piston:	hardened and ground steel	
Seals:	NBR (standard) FKM (optional, media temperature range -20°C to +120°C)	
10830 metric threads		
Complete valve: 0.47 kg		
Coil only:	0.23 kg	
	-	
850 mA, 18 ohm (24 V) 1750 mA, 4.1 ohm (12 V)		
120 – 150 Hz		
2 – 4% from In	om	
\leq 1 % of I _{nom}		
≤ 1 % of I _{nom}		
≤ 1 % of I _{nom}		
Coil50-1836	6	
in brochure 53.00	0	
	max. 80 bar (18; 20; 25 or 3 max. 40 l/min 100 cm³/min approx. 34 mn min20°C to 1 mydraulic oil to min. 7.4 mm²/s Class 18/16/13 150 – 1200 ye according to D No orientation Valve body: Piston: Seals: 10830 metric to Complete valve Coil only: 850 mA, 18 co 1750 mA, 4.1 120 – 150 Hz 2 – 4% from In ≤ 1 % of Inom ≤ 1 % of Inom	

see "Conditions and Instructions for Valves" in brochure 53,000


EN 5.990.7.0/06.19

TYPICAL PERFORMANCE

measured at v = 34 mm²/s, T_{oil} = 46°C

Typical characteristics are subject to specimen variance!

p-I characteristics



MODEL CODE	
<u>PDR10830-01</u> - <u>C</u> - <u>N</u> - <u>25</u>	- 24 <u>PG</u> - <u>18</u>
Basic model Proportional pressure control valve, direct-acting	
Type 01 = standard	
Body and ports* C = Cartridge only *versions with in-line bodies on request	
Seals N = NBR (standard) V = FKM	
Setting pressure range 18 = 18 bar 20 = 20 bar 25 = 25 bar 32 = 32 bar other pressure ranges on request	
Coil voltage0= No coil12= 12 V DC24= 24 V DCother voltages on request	
Coil connectors (type 50-1836)DC: PG = DIN connector according to EN 175301-803PL = 2 flying leads, 457 mm long; 0.75 mm²PN = Deutsch connector, 2-pole, axial,PU = AMP Junior Timer, 2-pole, axialother connectors on request	
$\begin{tabular}{lllllllllllllllllllllllllllllllllll$	
Standard models	
Model code	Part no.
PDR10830-01-C-N-18-0	3720405
PDR10830-01-C-N-18-12PU-4.1	3843400
PDR10830-01-C-N-18-24PG-18.0	4071846


FDR 10030-01-C-N-10-12F0-4.1	3043400
PDR10830-01-C-N-18-24PG-18.0	4071846
PDR10830-01-C-N-20-0	3720406
PDR10830-01-C-N-25-0	3692632
PDR10830-01-C-N-32-0	3692633
Other models on request	

*Standard in-line bodies


Standard III-III e bodies				
Code	Part no.	Material	Ports	Pressure
Geh (R10830-01X-01)	3583051	Steel	BSP 1/2	100 bar
Other connection housings on request				

Seal kits

Code	Material	Part no.
Seal kit 10830-NBR	NBR	3722246
Seal kit 10830-FKM	FKM	3726876







- *** Largest pre-drilling diameter (nominal tool diameter diameter)

Form tools

		÷
Tool	Part no.	
Countersink	3686093	\sim
Reamer	3686254	Millimetres Subject to technical modifications

Note The information in this brochure relates to the operating conditions and applications described. For applications not described, please contact the relevant technical department. Subject to technical modifications.

HYDAC Fluidtechnik GmbH Justus-von-Liebig-Str. D-66280 Sulzbach/Saar Tel.: 0 68 97 /509-01 Fax: 0 68 97 /509-598 E-mail: valves@hydac.com

 2.4 ± 0.2

42°

#