


# YDAC INTERNATIONAL

Up to 19 l/min Up to 250 bar

### **FUNCTION**



When the solenoid coil is de-energized, the valve blocks flow in both directions. When energized the valve allows flow in both directions.

## 2/2 Solenoid Directional Valve **Poppet Type, Direct Acting** Normally Closed Metric Cartridge - 250 bar


WSM06020W-01


#### **FEATURES**

- Excellent switching performance by high power HYDAC solenoid
- Hardened and ground control piston to ensure minimal wear and extended
- Low pressure drop due to CFD optimized flow path
- Coil seals protect the solenoid system
- External surfaces zinc-plated and corrosion-proof
- Compact design enables space-saving installation in connection housings and control blocks

#### **SPECIFICATIONS**

Operating pressure:	max. 250 bar			
Nominal flow:	max. 19 l/min	max. 19 l/min		
Internal leakage:	Leakage-free			
C		0,25 cm³/min at 350 bar)		
Media operating temperature range:	min20 °C to ı	min20 °C to max. +100 °C		
Ambient temperature range:	min20 °C to	min20 °C to max. +60 °C		
Operating fluid:	Hydraulic oil to	Hydraulic oil to DIN 51524 Part 1 and 2		
Viscosity range:	10 to 420 mm <sup>2</sup> /	10 to 420 mm²/s		
Filtration:	Class 21/19/16 cleaner	Class 21/19/16 according to ISO 4406 or		
MTTF <sub>d</sub> :	150 years (see	150 years (see "Conditions and		
		instructions for valves" in brochure 5.300)		
Installation:		No orientation restrictions		
Materials:	Valve body:	free-cutting steel		
	Poppet:	hardened and ground steel		
	Seals:	NBR (standard) FKM (optional, media temperature range -20 °C to +120 °C)		
	Back-up rings:			
	Coil:	steel / polyamide		
Cavity:	06020	, , , , , , , , , , , , , , , , , , ,		
Weight:	Valve complete	e 0.33 kg		
ŭ	Coil only	0.19 kg		
Electrical data:				
Type of voltage:		DC solenoid, AC voltage is rectified using a bridge rectifier built into the coil		
Nominal voltage:	1.5 A at 12 V D	1.5 A at 12 V DC 0.8 A at 24 V DC		
Voltage tolerance:		± 15% of the nominal voltage		
Coil duty rating:		Continuous up to max. 115%		
		of the nominal voltage at		
	60 °C ambient temperature			
Response time:				
	De-energized:	De-energized: approx. 50 ms		
Coil type:	Coil40-1836	Coil40-1836		





### **MODEL CODE** WSM06020W - 01 M - C - N - 24 DGBasic model Directional poppet valve, metric 01 = standard Manual override No details = without manual override M = manual override Body and ports\* = cartridge only **Seals** = NBR (standard) Ν = FKM Nominal voltage for actuating solenoid DC voltages: 12 = 12 V DC 24 = 24 V DC AC voltages (bridge rectifier built into the coil) 115 = 115 V AC 230 = 230 V AC Other voltages on request Coil connectors (type 40-1836)

DC: DG = DIN connector to EN175301-803 DT = AMP Junior Timer, 2-pole, radial

DK = Kostal threaded connection M27 x 1 DL = 2 flying leads 475 mm long, 0.75 mm<sup>2</sup>
DN = Deutsch connector, axial

AC: AG = DIN connector to EN175301-803

Other connectors on request

#### Standard models

Model code	Part No.
WSM06020W-01-C-N-24DG	3055971
WSM06020W-01-C-N-230AG	3055969


#### \*Standard in-line bodies

Code	Part No.	Material	Ports	Pressure
R06020-01X-01	275266	Steel, zinc-plated	G 3/8	420 bar
Other housings on r	equest			

#### Seal kits

millimeter subject to technical modifications

Code	Material	Part No.
SEAL KIT 06020	NBR	3119017
SEAL KIT 06020	FKM	3262477



#### **NOTE**

The information in this brochure relates to the operating conditions and applications described. For applications or operating conditions not described, please contact the relevant technical department.
Subject to technical modifications.

**HYDAC Fluidtechnik GmbH** Justus-von-Liebig-Str. D-66280 Sulzbach/Saar Tel: 0 68 97 /509-01 Fax: 0 68 97 /509-598 E-Mail: flutec@hydac.com