
# EN **5.946.1**.3/11.18




# (DAY) INTERNATIONAL



## 2/2 Solenoid Directional Valve **Poppet Type, Pilot Operated Normally Closed (Reverse Flow)** Metric Cartridge Valve - 350 bar

WSM10120ZR-01

#### **FUNCTION**



## **FEATURES**

- Coil seals protect the solenoid system
- Wide variety of connectors available
- Excellent switching performance by high power HYDAC solenoid
- Exposed surfaces zinc-nickel plated for increased corrosion protection (1.000 h Salt spray test)

### SPECIFICATIONS\*

- ·	0501		
Operating pressure:	max. 350 bar		
Nominal flow:	max. 75 l/min		
Internal leakage:	Leakage-free		
		0,25 cm <sup>3</sup> /min) at 350 bar	
Media operating temperature range:	min20 °C to max. +100 °C		
Ambient temperature range:	min20 °C to max. + 60 °C		
Operating fluid:	Hydraulic oil to DIN 51524 Part 1, 2 and 3		
Viscosity range:	min. 10 mm <sup>2</sup> /s to max. 420 mm <sup>2</sup> /s		
Filtration:	Class 21/19/16 according to ISO 4406 or cleaner		
MTTF <sub>d</sub> :	150 - 1200 years,		
	according to DIN EN ISO 13849-1		
Installation:	No orientation restrictions		
Materials:	Valve body:	free-cutting steel	
	Poppet:	hardened and ground steel	
	Seals:	NBR (standard) FKM (optional, media temperature range -20 °C to 120 °C)	
	Back-up rings:	PTFE	
Cavity:	10120		
Weight:	Valve complete:	0.37 kg	
-	Coil only:	0.19 kg	
Electrical data			
Type of voltage:	DC: direct current solenoid AC: alternating current solenoid with a bridge rectifier built into the coil		
Current draw at 20 °C:	1.5 A at 12 V DC 0.8 A at 24 V DC		
Voltage tolerance:	± 15 % of the nominal voltage		
Coil duty rating:	Continuous up to max. 115 % of the nominal voltage at 60 °C ambient temperature		
Response time:	energized:	approx. 35 ms	
(at $p_{max}$ , $Q_{max}$ , $v = 33 \text{ mm}^2/\text{s}$ )	de-energized:	approx. 80 ms	
	substantially extended response times possible at other operating conditions		
Coil type:	Coil40-1836		

The directional valve is a pilot operated valve in poppet style.


When the solenoid coil is not energized, the valve is closed from port 2 to port 1. Flow is permitted from port 1 to port 2. When energized the valve allows flow in both directions.

Please mind: In pilot operated solenoid valves, shift performance and response times depend i.a. very much on pressure drop and volume flow during actuation.

#### **DIMENSIONS** Manual override torque 4<sup>+1</sup> Nm After loosening knurled After loosening the mounting nut, the coil can be rotated through nut, manual operation is possible by twisting button 360° and removed anticlockwise. ø36.3 23.8 torque 4<sup>+1</sup> Nm 72 28 0 hex. SW32 (2) $\oplus$ 330 Steel manifold (ultimate tensile strength < 360 N/mm²): (1)Ø19 Aluminium manifold (ultimate tensile strength < 330 N/mm²): M22 x1.5 60 Nm ø27 (tool acc. to DIN EN ISO 6789. tool type II class A or B) For further informations see brochure No. 53.000 "Conditions and instructions for valves"

millimeter subject to technical modifications

#### **CAVITY**




Part No.

1014206

170418

#### **MODEL CODE**



DC voltages = 12 V DC 24 = 24 V DC

AC voltages (bridge rectifier built into the coil)

115 = 115 V AC 230 = 230 V AC

Other voltages on request

#### Coil connectors (type 40-1836)

DC: DG = DIN connector type A to EN 175301-803 DK = KOSTAL-threaded connection M27x1 DL = 2 flying leads, 457 mm long; 0.75 mm<sup>2</sup> DN = Deutsch connector, 2-pole, axial

DT = AMP Junior Timer, 2-pole, radial

AC: AG = DIN connector type A to EN 175301-803

Other connectors on request

#### Standard models

Model code	Part No.
WSM10120ZR-01-C-N-24DG	3179188
WSM10120ZR-01-C-N-230AG	3179187

#### \*Standard in-line bodies

Code	Part No.	Material	Ports	Pressure
R10120-01X-01	395234	Steel, zinc-plated	G1/2"	350 bar


For other connection housings, see brochure no. E 5.252.

#### Seal kits

Code	Part No.
FS METRISCH 1012./N	3651295
FS METRISCH 1012./V	3651296

#### TYPICAL PERFORMANCE

Measured at  $v = 33 \text{ mm}^2/\text{s,T}_{oil} = 46 ^{\circ}\text{C}$ 



millimeter subject to technical modifications

The information in this brochure relates to the operating conditions and applications described. For applications or operating conditions not described, please contact the relevant technical department.
Subject to technical modifications.

**HYDAC Fluidtechnik GmbH** Justus-von-Liebig-Str. D-66280 Sulzbach/Saar Tel: 0 68 97 /509-01 Fax: 0 68 97 /509-598 E-Mail: valves@hydac.com

Countersink (shank MK3)

Reamer (shank MK2)

Tool