



## Description:

The pressure transmitter HDA 4700 in ATEX version has been specially developed for use in potentially explosive atmospheres and is based on the HDA 4000 series.

As with the industry model, the HDA 4700 in ATEX version has a stainless steel measurement cell with thin-film strain gauge.

Intended areas of application are, for example, in the oil and gas industry, in mining, on gas turbines or in locations with high levels of dust contamination, e.g. in mills.

## Protection types and applications:

I M1 Ex ia I Ma

II 1G Ex ia IIC T6 Ga  
 II 1/2G Ex ia IIC T6 Ga/Gb  
 II 2G Ex ia IIC T6 Gb  
 II 3G Ex nA IIC T6, T5, T4 Gc  
 II 3G Ex ic IIC T6, T5, T4 Gc

II 1D Ex ia IIIC T85°C Da  
 II 1D Ex ta IIIC T80/90/100°C Da  
 T<sub>500</sub> T90/T100/T110°C Da

II 2D Ex tb IIIC T80/90/100°C Db  
 II 3D Ex tc IIIC T80/T90/T100°C Dc  
 II 3D Ex ic IIIC T80/T90/T100°C Dc

## Special features:

- Accuracy  $\leq \pm 0.25\%$  FS B.F.S.L.
- Certificates:  
 KEMA 05ATEX1016 X  
 KEMA 05ATEX1021
- Output signal 4 .. 20 mA
- Very small temperature error
- Excellent EMC characteristics
- Excellent durability

## Electronic Pressure Transmitter

### HDA 4700

ATEX Intrinsically Safe  
 ATEX Dustproof Enclosure  
 ATEX Non-sparking



## Technical data:

| Input data   |  |
|--|--|
| Measuring ranges <sup>1)</sup>                           | 150, 500, 750, 1000, 1500, 3000, 5000, 6000, 9000, 15000 psi   |
| Overload pressures                                       | 290, 1160, 1740, 2900, 2900, 7250, 11600, 11600, 14500, 23200 psi  |
| Burst pressures  | 1450, 2900, 4350, 7250, 7250, 14500, 29000, 29000, 29000, 43500 psi  |
| Mechanical connection <sup>1)</sup>                      | SAE 6 9/16-18 UNF 2A<br>SF 250 CS20, Autoclave(7/16-20-UNF 2B)   |
| Torque value   | 15lb-ft(20Nm) - SAE 6<br>30lb-ft(40Nm) SF 250 CX20   |
| Parts in contact with medium                             | Stainless steel: 1.4542; 1.4571; 1.4435;<br>1.4404; 1.4301<br>Seal: FPM  |
| Output data  |  |
| Output signal permitted load resistance                  | 4 .. 20 mA, 2 conductor<br>$R_{Lmax} = (U_B - 12 V) / 20 \text{ mA} [\text{k}\Omega]$                                  |
| Accuracy to DIN 16086, Max. setting                      | $\leq \pm 0.25\%$ FS typ.<br>$\leq \pm 0.5\%$ FS max.  |
| Accuracy at min. setting (B.F.S.L.)                      | $\leq \pm 0.15\%$ FS typ.<br>$\leq \pm 0.3\%$ FS max.  |
| Temperature compensation                                 | 0.0045% FS/°F typ.   |
| Zero point   | 0.0085% FS/°F max.   |
| Temperature compensation                                 | 0.0045% FS/°F typ.   |
| Over range   | 0.0085% FS/°F max.   |
| Non-linearity at max. setting to DIN 16086               | $\leq \pm 0.3\%$ FS max.   |
| Hysteresis   | $\leq \pm 0.1\%$ FS max.   |
| Repeatability  | $\leq \pm 0.05\%$ FS   |
| Rise time  | $\leq 1.5 \text{ ms}$  |
| Long-term drift  | $\leq \pm 0.1\%$ FS typ. / year  |
| Environmental conditions                                 |  |
| Compensated temperature range                            | -4..+185°F   |
| Operating temperature range <sup>2)</sup>                | -40..+140°F / -4..+140°F   |
| Storage temperature range                                | -40 to 212°F   |
| Fluid temperature range <sup>2)</sup>                    | -20..+140°F<br>40..+140°F / -4..+140°F   |
| CE mark  | EN 61000-6-1 / 2 / 3 / 4<br>EN 60079-0 / 11 / 26 / 31<br>EN 50303  |
| Vibration resistance to DIN EN 60068-2-6 at 10 .. 500 Hz | $\leq 20 \text{ g}$  |
| Protection class to IEC 60529                            | IP 65 (for male EN175301-803 (DIN 43650) and Binder 714 M18)<br>IP 67 (for M12x1 male when an IP 67 connector is used) |
| Relevant data for Ex applications                        |  |
| Supply voltage   | Ex ia, ic: $U_i = 12 \dots 28 \text{ V}$<br>Ex nA, ta, tb, tc: 12 .. 28 V  |
| Max. input current                                       | Ex ia, ic: $I_i = 100 \text{ mA}$  |
| Max. input power   | Ex ia, ic: $P_i = 1 \text{ W}$<br>Ex nA, ta, tb, tc: max. power consumption $\leq 1 \text{ W}$                         |
| Connection capacitance of the sensor                     | $C_i = \leq 22 \text{ nF}$   |
| Inductance of the sensor                                 | $L_i = 0 \text{ mH}$   |
| Insulation voltage <sup>3)</sup>                         | 50 V AC, with integrated overvoltage protection EN 61000-6-2   |
| Other data   |  |
| Residual ripple of supply voltage                        | $\leq 5\%$   |
| Life expectancy  | $> 10$ million cycles<br>0 .. 100 % FS   |
| Weight   | $\sim 150 \text{ g}$   |

Note: Reverse polarity protection of the supply voltage, excess voltage, override and short circuit protection are provided.

FS (Full Scale) = relative to the full measuring range, B.F.S.L. = Best Fit Straight Line

<sup>1)</sup> 15000 psi only with mechanical connection SF 250 CX20, Autoclave

<sup>2)</sup> -4°F with FPM seal, -40°F on request

<sup>3)</sup> 500 V AC on request

## Areas of application:


| Code No. for use in Model code                | 1  |   | 9  |  | A   | C   |
|---|--|---|--|--|---|---|
| <b>Protection type</b>                        | I M1 Ex ia I Ma  | II 1G Ex ia IIC T6 Ga<br>II 1/2G Ex ia IIC T6 Ga/Gb<br>II 1D Ex ia IIIC T85 °C Da   | II 2G Ex ia IIC T6 Gb  | II 3G Ex nA IIC T6 Gc  | II 1D Ex ta IIIC T80 °C<br>T <sub>500</sub> T90 °C Da<br>II 2D Ex tb IIIC T80 °C Db         | II 3G Ex ic IIC T6 Gc<br>II 3D Ex ic IIIC T80 °C Dc   |
| <b>Certificate</b>                            | KEMA 05ATEX1016 X / KEMA 05ATEX1021  |   |  |  |   |   |
| <b>Zones / Categories</b>                     | Group I<br>Category M1<br>Mining<br>Protection class:<br>intrinsically safe ia<br>with barrier | Group II, III<br>Category 1G, 1/2G, 1D<br>Gases/conductive dust<br>Protection class:<br>intrinsically safe ia<br>with barrier | Group II<br>Category 2G<br>Gases<br>Protection class:<br>intrinsically safe ia<br>with barrier | Group II<br>Category 3G<br>Gases<br>Protection class:<br>Non-sparking nA | Group III<br>Category 1D, 2D<br>Conductive dust<br>Protection class:<br>Dustproof enclosure | Group II, III<br>Category 3G, 3D<br>Gases/conductive dust<br>Protection class:<br>Intrinsically safe ic<br>with barrier |
| <b>Electrical Connection (see model code)</b> | 4, 5, 6  | 4, 5, 6   | 4, 5, 6  | 6  | 6   | 4,5,6   |

Devices in ignition protection class "Dustproof enclosure" for the protection types II 1D Ex ta IIIC T80/90/100 °C Da T<sub>500</sub>T90/T100/T110 °C Da, II 2D Ex tb IIIC T80/90/100 °C Db and II 3D Ex tc IIIC T80/90/100 °C Dc are available with flying leads on request.

Devices in the ignition protection class "Non-sparking" for the protection type II 3G Ex nA IIC T6, T5, T4 Gc are available with flying leads on request.

## Pin connections:


Binder series 714 M18



Pin HDA 47X4-A

|   |          |
|---|----------|
| 1 | n.c.     |
| 2 | Signal + |
| 3 | Signal - |
| 4 | n.c.     |


EN175301-803 (DIN 43650)



Pin HDA 47X5-A

|   |          |
|---|----------|
| 1 | Signal + |
| 2 | Signal - |
| 3 | n.c.     |
| ⊥ | Housing  |

M12x1



Pin HDA 47X6-A

|   |          |
|---|----------|
| 1 | Signal + |
| 2 | n.c.     |
| 3 | Signal - |
| 4 | n.c.     |

## Model code:

**HDA 4 7 X X - A - XXXX - A X X - 000 (PSI)**

### Mechanical connection

7 = SAE 6, 9/16-18 UNF 2A male  
C = SF 250 CX20, Autoclave  
(only for "15000 psi" press.  
range)

### Electrical connection

4 = Male, 4 pole Binder series 714 M18  
(connector not supplied)  
5 = Male, 3 pole + PE, EN175301-803  
(DIN 43650)  
(connector supplied)  
6 = Male, M12x1, 4 pole  
(connector not supplied)

### Signal

A = 4 .. 20 mA, 2 conductor

### Pressure ranges in psi

0150, 0500, 0750, 1000, 1500, 3000, 5000, 6000, 9000  
15000 psi (only in conjunction with mechanical connection  
type "C")

### Approval

A = ATEX

### Insulation voltage

N = 50 V AC

### Protection types and applications (code)

1 = I M1 Ex ia I Ma  
II 1G Ex ia IIC T6 Ga  
II 1/2G Ex ia IIC T6 Ga/Gb  
II 2G Ex ia IIC T6 Gb  
II 1D Ex ia IIIC T85 °C Da  
9 = II 3G Ex nA IIC T6 Gc (only in conjunction with electr. connection "6")\*  
A = II 1D Ex ta IIIC T80 °C T<sub>500</sub>T90 °C Da (only in conjunction with electr.  
connection "6")\*  
II 2D Ex tb IIIC T80 °C Db  
C = II 3G Ex ic IIC T6 Gc  
II 3D Ex ic IIIC T80 °C Dc

### Modification number

000 = Standard

### Notes:


\* For design and electrical connection see device dimensions

### Accessories:


Appropriate accessories, such as electrical connectors, can be found  
in the Accessories brochure.

## Dimensions:

Protection types and applications (code): 1, C



Protection ratings and areas of application (code): 9, A



The impact protected metal safety sleeve is included. A straight female connector is required for electrical connection; e.g. female connector M12x1, 4 pole, straight, with 3m shielded cable: ZBE 06S-03, Part No. 6098243

## Note:

The information in this brochure relates to the operating conditions and applications described.

For applications or operating conditions not described, please contact the relevant technical department.

Subject to technical modifications.

For European mechanical connection and bar ranges see European Catalog

