


## Flow Divider / Combiner UNF Cartridge – 350 bar ST10-01

### FUNCTION



**Note:**  
Port 1 is not used

The flow divider is a spring-loaded pressure compensated spool type valve. It divides a flow in two and keeps both flows constant. The division is made according to the specified ratio - from port 3 to ports 2 and 4. As a flow combiner it combines two partial flows together – from ports 2 and 4 to port 3. Port 1 is not used.

### FEATURES



- Can be used for differential locks in drive applications
- Excellent dividing and combining accuracy
- Synchronizing flow in both operating modes
- Wide flow range down to 25% of nominal flow rating
- Compact design
- Exposed surfaces zinc-nickel plated for increased corrosion protection (1.000 h Salt spray test)

### SPECIFICATIONS\*


Operating pressure:	max. 350 bar	
Nominal flow:	max. 45 l/min	
Inlet flow:	7.6 l/min	Code 11
	15.2 l/min	Code 22
	22.8 l/min	Code 33
	30.4 l/min	Code 44
	37.8 l/min	Code 55
	45.6 l/min	Code 66
Dividing accuracy:	up to 10% of inlet flow per partial flow	
Media operating temperature range:	min. -30 °C to max. +100 °C	
Ambient temperature range:	min. -30 °C to max. +100 °C	
Operating fluid:	Hydraulic oil to DIN 51524 Part 1, 2 and 3	
Viscosity range:	min. 7.4 mm <sup>2</sup> /s to max. 420 mm <sup>2</sup> /s	
Filtration:	Class 21/19/16 to ISO 4406 or cleaner	
MTTF <sub>d</sub> :	150 - 1200 years*	
Materials:	Valve body:	steel
	Spool:	hardened and ground steel
	Seals:	NBR (standard) FKM (optional, media temperature range -20 °C to +120 °C)
	Back-up rings:	PTFE
Cavity:	FC10-4 (port 1 not used)	
Weight:	0.122 kg	

\*see hints and conditions for valves" in brochure 53.000

## DIMENSIONS



## CAVITY



### Form tools

Tool	Part No.
Countersink FC10-4	176174
Reamer FC10-4	176175

millimeter (inch)  
subject to technical modifications

## MODEL CODE

**ST10-01 - C - N - 33**

**Basic model**  
Flow divider / Combiner, UNF

**Body and ports\***  
C = cartridge only  
SB4 = G1/2 ports, steel body  
AB4 = G1/2 ports, aluminium body

**Seals**  
N = NBR (standard)  
V = FKM

### Flow rate code & flow range

Code	Ratio Port 2 [%]	Ratio Port 4 [%]	Max. inlet flow [l/min]	Balance flow rate	
				Combining [l/min] at 100 bar	Dividing [l/min] at 100 bar
11	50	50	7.6	0.7	0.7
22	50	50	15.2	1.3	1.1
33	50	50	22.8	2.3	2.1
44	50	50	30.4	2.6	2.8
55	50	50	37.8	3	3.4
66	50	50	45.6	5.2	3.1

### Standard models

Model code	Part No.
ST10-01-C-N-11	562884
ST10-01-C-N-22	562885
ST10-01-C-N-33	562886
ST10-01-C-N-44	562887
ST10-01-C-N-55	562888
ST10-01-C-N-66	562889

### \*Standard in-line bodies



Code	Part No.	Material	Ports	Pressure
FH104-SB4	3037784	Steel, zinc-plated	G1/2"	420 bar
FH104-AB4	3038097	Aluminium, anodized	G1/2"	210 bar

### Seal kits

Code	Material	Part No.
FS UNF 10/N SEAL KIT	NBR	3651557
FS UNF 10/V SEAL KIT	FKM	3651559

## PERFORMANCE

Measured at  $v = 34 \text{ mm}^2/\text{s}$   $T_{\text{Oil}} = 46 \text{ }^\circ\text{C}$



typical characteristic  
subject to tolerances

### NOTE

The information in this brochure relates to the operating conditions and applications described. For applications or operating conditions not described, please contact the relevant technical department.  
Subject to technical modifications.

**HYDAC Fluidtechnik GmbH**

Justus-von-Liebig-Str.  
**D-66280 Sulzbach/Saar**  
Tel: 0 68 97 /509-01  
Fax: 0 68 97 /509-598  
E-Mail: flutec@hydac.com