


LOW PRESSURE FILTERS


FLND Series

Inline Duplex Filters

360 psi • up to 100 gpm



Hydraulic Symbol



Features

- Lightweight duplex filter constructed of aluminum.
- Aluminum alloy is water tolerant - anodization is not required for high water based fluids (HWBF).
- The filter housings are designed to withstand pressure surges as well as high static pressure loads.
- The screw-in bowl allows the filter element to be easily removed for replacement or cleaning.
- A visual (pop-up), electrical, electrical/visual (lamp), or electronic differential type clogging indicator are possible.
- The standard model is supplied with vent and drain plugs, and also a connection for differential clogging indicator.
- The pressure is equalized between chambers by raising the change-over lever prior to switching it to the relevant filter side. Thus, the filter contains an integrated equalization valve.
- CRN Approval Available. (*Canadian Registration Number*)
- Bypass versions of FLND filters have the bypass valve located in the filter head.
- This filter can be modified to meet the requirements of DIN 24550* as follows:
 - Filter size 0160 with G 1-1/4" port selection
 - Filter size 0250 with G 1-1/2" port selection
 - Filter size 0400 with SAE-DN 38 1-1/2" Flange

*Note - QPD design does not meet DIN 24550.

Technical Specifications

| | | |
|---|--|-----------------------|
| Mounting Method | 4 mounting holes - filter head | |
| Port Connection | Inlet / Outlet 1-1/4" Threaded – SAE 20, 1-1/4" BSPP 1-1/2" Threaded – SAE 24, 1-1/2" BSPP 1-1/2" Flange-SAE-DN 38 Code 61 | |
| Flow Direction | Inlet: Side | Outlet: Opposite Side |
| Construction Materials | Head, Bowl Aluminum | |
| Flow Capacity | 160 42 gpm (160 lpm) 250 66 gpm (250 lpm) 400 105 gpm (400 lpm) | |
| Housing Pressure Rating | Max. Operating Pressure 360 psi (25 bar) Fatigue Pressure 360 psi (25 bar) Burst Pressure 1450 psi (100 bar) | |
| Element Collapse Pressure Rating | BN4HC, W/HC 290 psid (20 bar) | |
| Fluid Temperature Range | 14°F to 212°F (-10°C to 100°C) Consult HYDAC for applications below 14°F (-10°C) | |
| Fluid Compatibility | Compatible with all hydrocarbon based, synthetic, water glycol, oil/water emulsion, and high water based fluids when the appropriate seals are selected. | |
| Indicator Trip Pressure | $\Delta P = 36$ psid (2.5 bar) -10% $\Delta P = 72$ psid (5 bar) -10% $\Delta P = 116$ psid (8 bar) -10% (<i>non-bypass</i>) | |
| Bypass Valve Cracking Pressure | $\Delta P = 50.75$ psid (3.5 bar) +10% $\Delta P = 102$ psid (7 bar) +10% | |

Applications



Automotive



Gearboxes



Industrial



Power Generation



Pulp & Paper



Shipbuilding



Steel / Heavy Industry

Model Code

FLND BN/HC 250 D D F 10 B 1 . X / 12 - V - QPD - B3.5

Filter Type _____
 FLND = Inline duplex filter

Element Media _____
 BN/HC = Betamicon® (Low Collapse) W/HC = Wire Mesh

Size _____
 160, 250, 400

Operating Pressure _____
 D = 360 psi (25 bar)

Type of Change-Over _____
 D = segment valve

Port Type / Size _____
 E = 1-1/4" SAE or BSPP Threaded
 F = 1-1/2" SAE or BSPP Threaded
 K = 1-1/2" Flange-SAE-DN 38 Code 61 Flange

Filtration Rating (micron) _____
 3, 6, 10, 25 = BN/HC 25, 50, 100, 200 = W/HC

Type of ΔP Clogging Indicator _____
 A, B, BM, C, D (Others available upon request, see Clogging Indicators section.)

Type Code _____
 1

Modification Number (latest version is always supplied) _____

Port Configuration _____
 (omit) = SAE DN Flange
 0 = BSPP Threaded inlet/outlet
 12 = SAE straight thread inlet/outlet

Seals _____
 (omit) = Nitrile rubber (NBR)
 V = Fluorocarbon elastomer (FKM) (standard)

Version _____
 (omit) = meets DIN 24550
 QPD = Quality Protection Design

Bypass Valve _____
 (omit) = no bypass (optional)
 B3.5 = 50.75 psid (3.5 bar) (standard)
 B7 = 101.5 psid (7 bar) (optional)

Supplementary Details _____
 L24, L48, L110, L220 = Lamp for D-type clogging indicator (LXX, XX = voltage)
 RL = Flow Path reversed - Right inlet/Left outlet CRN = CRN Approval
 EM = Air Bleed Valves SFREE = Element specially designed to minimize electrostatic charge generation
 VKD = Drain Valves cRUUs = Electrical Indicator with underwriter's approval
 SO263 = Modification of elements for Skydrol or HYJET phosphate ester fluids
 SO376 = Modification of ON and W/HC elements for HFA, HFB, HFC, and HFD flame retardant liquids

Replacement Element Model Code

0250 DN 010 BN4HC / V QPD

Size _____
 0160, 0250, 0400

Type _____
 DN

Filtration Rating (micron) _____
 3, 6, 10, 25 = BN4HC
 25, 50, 100, 200 = W/HC

Element Media _____
 BN4HC, W/HC

Seals _____
 (omit) = Nitrile rubber (NBR)
 V = Fluorocarbon elastomer (FKM) (standard)

Version _____
 (omit) = meets DIN 24550
 QPD = Quality Protection Design

Supplementary Details _____
 SO263 = (same as above)
 SFREE = (same as above)
 SO376 = (same as above)

Clogging Indicator Model Code

VM 2.5 B . X / V

Indicator Prefix _____
 VM = G 1/2 3000 psi

Trip Pressure _____
 2.5 = 36 psid (2.5 bar)] (optional)
 5 = 72 psid (5 bar)

Type of Indicator _____
 A = no indicator, plugged port
 B = pop-up indicator (auto reset)
 BM = pop-up indicator (manual reset)
 C = Electric switch - SPDT
 D = Electric switch and light - SPDT

Modification Number _____

Supplementary Details _____

Seals _____
 (omit) = Nitrile rubber (NBR)
 V = Fluorocarbon elastomer (FKM) (standard)

Light Voltage (D type indicators only) _____
 L24 = 24V L110 = 110V

Thermal Lockout (VM, VD types C, D, J, and J4 only) _____
 T100 = Lockout below 100°F


Underwriters Approval (VM, VD types C, D, J, and J4 only) _____
 cRUUs = Electrical Indicator with underwriter's approval

(For additional details and options, see Clogging Indicators section.)



Model Codes Containing RED are non-stock items — Minimum quantities may apply — Contact HYDAC for information and availability

LOW PRESSURE FILTERS


Dimensions FLND



-DDE
1 5/8"-12UN-2B
SAE-20
OR
-DDF
1 7/8"-12UN-2B
SAE-24
OR
-DDK
1 1/2" SAE DN 38
Flange



| Model | Mounting Hole |
|-------------------|-----------------------|
| FLND160-400DDE | M10-1.5 x 19mm Deep |
| FLND160-400DDE/12 | 3/8-24UNF x 14mm Deep |
| FLND160-400DDF | M10-1.5 x 19mm Deep |
| FLND160-400DDF/12 | 3/8-24UNF x 14mm Deep |
| FLND160-400DDK | M10-1.5 x 19mm Deep |



Before changing the element, relieve pressure in the filter housing.

| Size | 160 | 250 | 400 |
|---------------|------|------|------|
| Weight (lbs.) | 20.1 | 21.2 | 26.5 |

Dimensions shown are [inches] millimeters for general information and overall envelope size only. Weights listed include element.
For complete dimensions please contact HYDAC to request a certified print.

Sizing Information

Total pressure loss through the filter is as follows:


Assembly $\Delta P = \text{Housing } \Delta P + \text{Element } \Delta P$

Housing Curve:

Pressure loss through housing is as follows:

Housing $\Delta P = \text{Housing Curve } \Delta P \times \frac{\text{Actual Specific Gravity}}{0.86}$

Adjustments must be made for viscosity & specific gravity of the fluid to be used! (see "Sizing HYDAC Filter Assemblies" in Section B - Overview)



Element K Factors

$\Delta P \text{ Elements} = \text{Elements (K) Flow Factor} \times \text{Flow Rate (gpm)} \times \frac{\text{Actual Viscosity (SUS)}}{141 \text{ SUS}} \times \frac{\text{Actual Specific Gravity}}{0.86}$
(From Tables Below)

| BN4HC | ...DN...BN4HC (Betamicron Low Collapse) | | | |
|-------------------|---|-----------------|------------------|------------------|
| | 3 μm | 6 μm | 10 μm | 25 μm |
| 0160 DN XXX BN4HC | 0.434 | 0.280 | 0.187 | 0.143 |
| 0250 DN XXX BN4HC | 0.280 | 0.176 | 0.115 | 0.099 |
| 0400 DN XXX BN4HC | 0.176 | 0.110 | 0.071 | 0.055 |

| W/HC | ...DN...W/HC (Betamicron Low Collapse) | | | |
|------------------|--|------------------|-------------------|-------------------|
| | 25 μm | 50 μm | 100 μm | 200 μm |
| 0160 DN XXX W/HC | 0.009 | 0.009 | 0.009 | 0.009 |
| 0250 DN XXX W/HC | 0.006 | 0.006 | 0.006 | 0.006 |
| 0400 DN XXX W/HC | 0.004 | 0.004 | 0.004 | 0.004 |

All Element K Factors in psi / gpm.

FLND 160/250/400

