


HIGH PRESSURE FILTERS


HF3P Series

Inline Filters

6090 psi • up to 120 gpm



Hydraulic Symbol



Features

- Non-welded housing design reduces stress concentrations and prevents fatigue failure.
- Inlet/Outlet port options include SAE straight thread O-ring boss, BSPP and flange mounting to allow easy installation without costly adapters.
- O-ring seals are used to provide positive, reliable sealing. Choice of O-ring materials (nitrile rubber, fluorocarbon elastomer, ethylene propylene rubber) provides compatibility with petroleum oils, synthetic fluids, water-glycols, oil/water emulsions, and high water based fluids.
- Screw-in bowl or lid (on 2 piece bowls), mounted below the filter head requires minimal clearance to remove the element for replacement, and contaminated fluid cannot be washed downstream when element is serviced.
- Clogging indicators are actuated by differential pressure and have no external dynamic seal. High reliability is achieved and magnetic indicator actuation eliminates a potential leak point.
- A poppet type bypass valve, located in filter head, mounted between the inlet and outlet port to provides positive sealing during normal operation and fast response during cold starts and flow surges, while additionally providing low operating ΔP .
- Fatigue pressure rating equals maximum allowable working pressure rating.

Applications



Automotive



Construction



Industrial



Railways




Steel / Heavy Industry

Technical Specifications

Mounting Method	4 mounting holes
Port Connection	SAE-16, SAE-24, 1" BSPP, 1 1/2" BSPP, 1 1/2" SAE Flange Code 61, 2" SAE Flange Code 62
Flow Direction	Inlet: Side Outlet: Side
Construction Materials	
Head	Ductile iron
Bowl	Steel
Housing (size 16)	Steel
Cap (size 16)	Ductile iron
Flow Capacity	
4"	28 gpm (106 lpm)
8"	55 gpm (208 lpm)
13"	91 gpm (344 lpm)
16"	120 gpm (454 lpm)
Housing Pressure Rating	
Max. Allowable Working Pressure	6090 psi (420 bar)
Fatigue Pressure	6090 psi (420 bar) @ 1 million cycles
Burst Pressure	15,080 psi (1040 bar)
Element Collapse Pressure Rating	
BH	3045 psid (210 bar)
BN	290 psid (20 bar)
Fluid Temperature Range	14°F to 212°F (-10°C to 100°C) Consult HYDAC for applications operating below 14°F (-10°C)
Fluid Compatibility	
Compatible with all hydrocarbon based, synthetic, water glycol, oil/water emulsion, and high water based fluids when the appropriate seals are selected.	
Indicator Trip Pressure	
$\Delta P = 29$ psid (2 bar) -10% (optional)	
$\Delta P = 72$ psid (5 bar) -10% (standard)	
$\Delta P = 116$ psid (8 bar) -10% (optional)	
Bypass Valve Cracking Pressure	
$\Delta P = 43$ psid (3 bar) +10% (optional)	
$\Delta P = 87$ psid (6 bar) +10% (standard)	
Non Bypass Available	


Model Code

HF3P BN 08 T F 3 B 1 . X / 12 V B6




Replacement Element Model Code

1 . 11 . 08 D 03 BN / V



Clogging Indicator Model Code

VD 5 C . X / V





Model Codes Containing RED are non-stock items — Minimum quantities may apply — Contact HYDAC for information and availability

HIGH PRESSURE FILTERS




Dimensions

HF3P-04/08/13/16

	a	b	c	d
1-1/2" Code 61	(1.406) 35.71	(2.750) 69.85	1/2-13UNC-2B	(0.87) 22
2" Code 62	(1.750) 44.45	(3.812) 96.80	3/4-10UNC-2B	(0.98) 25



HF3P-16



Size	04	08	13	16
Weight (lbs.)	49.2	56.1	72.5	107.3

Dimensions shown are [inches] millimeters for general information and overall envelope size only. Weights listed include element. For complete dimensions please contact HYDAC to request a certified print.

Sizing Information

Total pressure loss through the filter is as follows:


Assembly $\Delta P = \text{Housing } \Delta P + \text{Element } \Delta P$

Housing Curve:

Pressure loss through housing is as follows:

Housing $\Delta P = \text{Housing Curve } \Delta P \times \frac{\text{Actual Specific Gravity}}{0.86}$

Adjustments must be made for viscosity & specific gravity of the fluid to be used! (see "Sizing HYDAC Filter Assemblies" in Section B - Overview)



Element K Factors

$\Delta P \text{ Elements} = \text{Elements (K) Flow Factor} \times \text{Flow Rate (gpm)} \times \frac{\text{Actual Viscosity (SUS)}}{141 \text{ SUS}} \times \frac{\text{Actual Specific Gravity}}{0.86}$
(From Tables Below)

Autospec HF3 Depth	1.11.08DXXBN (Low Collapse)			
Size	3 μm	6 μm	12 μm	25 μm
1.11.04DXXBN	0.590	0.500	0.266	0.153
1.11.08DXXBN	0.289	0.241	0.135	0.076
1.11.13DXXBN	0.175	0.146	0.082	0.046
1.11.16DXXBN	0.132	0.110	0.062	0.035

Autospec HF3 Depth	1.11.08DXXBH (High Collapse)			
Size	3 μm	6 μm	10 μm	17 μm
1.11.04DXXBH	0.937	0.660	0.401	0.210
1.11.08DXXBH	0.460	0.321	0.195	0.102
1.11.13DXXBH	0.274	0.193	0.117	0.615
1.11.16DXXBH	0.206	0.145	0.089	0.046

All Element K Factors in psi / gpm.