



# LOW PRESSURE FILTERS


## HF4R Series

In-Tank Return Line Filters

100 psi • up to 100 gpm



### Hydraulic Symbol



### Features

- Designed to meet and comply with HF4 Automotive standard and SAE J2066 standard.
- Inlet port options include SAE straight thread O-ring boss, SAE Flange, BSPP and NPT ports to allow easy installation without costly adapters.
- O-ring seals are used to provide positive, reliable sealing. Choice of Nitrile rubber (NBR), or Fluorocarbon elastomer (FKM) O-ring material provides compatibility with petroleum oils, synthetic fluids, water-glycols, oil/water emulsions, and water based fluids.
- In-tank design requires minimal space for installation.
- Provision is made for an additional inlet port to allow two return lines to be connected to the same filter.
- Filters include 1 1/2" threaded NPT outlet connection.

### Applications



Agricultural



Automotive



Construction



Gearboxes



Industrial



Steel / Heavy Industry

### Technical Specifications

<b>Mounting Method</b>	4 mounting holes - filter housing	
<b>Port Connection</b>	Inlet SAE-24, 1 1/2" NPT, 1 1/2" BSPP, 1 1/2" Flange, Code 61	
Outlet HF4R 09/18/27	1 1/2" NPT male	
<b>Flow Direction</b>	Inlet	Outlet
HF4R	Side	Bottom
<b>Construction Materials</b>	Head, Lid Aluminum Bowl Carbon Steel	
<b>Flow Capacity</b>	HF4R09 50 gpm (189 lpm) HF4R18 75 gpm (378 lpm) HF4R27 100 gpm (454 lpm)	
<b>Housing Pressure Rating</b>	Max. Allowable Working Pressure* 100 psi (7 bar) Fatigue Pressure Contact HYDAC Burst Pressure Contact HYDAC	
<b>Element Collapse Pressure Rating</b>	BN, BN4AM, AM, W, P/HC 145 psid (10 bar)	
<b>Fluid Temperature Range</b>	14°F to 212°F (-10°C to 100°C) Consult HYDAC for applications below 14°F (-10°C)	
<b>Fluid Compatibility</b>	Compatible with all hydrocarbon based, synthetic, water glycol, oil/water emulsion, and high water based fluids when the appropriate seals are selected.	
<b>Indicator Trip Pressure</b>	All Other Indicators P = 14.5 psi (1 bar) -10% P = 29 psi (2 bar) -10% P = 36 psi (2.5 bar) -10%	
	Gauges (E / ES) P = 11.6 psi (0.8 bar) P = 20 psi (1.4 bar) P = 29 psi (2 bar)	
<b>Bypass Valve Cracking Pressure</b>	$\Delta P = 25$ psid (1.7 bar) +10% (optional) $\Delta P = 40$ psid (2.7 bar) +10% (standard) $\Delta P = 50$ psid (3.4 bar) +10% (contact factory)	

\*Note: All HF4R Filters MAWP reduce to 101.5 psi (7 bar) when using the following "VR" indicators: B, BM, E, ES, GC, LE, LZ.  
Any filters incorporating a VMFXE.X/3 or VMFXES.X/3 static gauge indicator (1/8" NPT thread) will be de-rated to an MAWP of 60 psi (4 bar).

# LOW PRESSURE FILTERS

## Model Code

**HF4R BN 09 V F 3 C 1.X / 3 B2.7 C T**

**Filter Type** \_\_\_\_\_  
 HF4R = In-tank return filter

**Element Media** \_\_\_\_\_  
 BN = Betamicron® (Low Collapse) **BN/AM= Betamicron® Aquamicon®**  
 AM = Aquamicon® W = Wire Mesh  
 P = Polyester

**Element Length** \_\_\_\_\_  
 09 = Single Element Length (9")  
 18 = Double Element Length (18")  
 27 = Triple Element Length (27")

**Pressure Rating** \_\_\_\_\_  
 V = 100 psi (7 bar)  
 Y = 60 psi (4.1 bar), when "E" type static pressure gauge is used with a B1.7 bypass setting

**Type of Connection** \_\_\_\_\_  
 F = 1 1/2" Threaded (SAE-24, 1 1/2" NPT, or G/BSPP 1 1/2")  
 K = 1 1/2" Flanged (1 1/2" SAE Code 61)

**Filtration Rating (microns)** \_\_\_\_\_  
 3, 5, 10, 20 = BN 25, 50, 100, 200 = W 3, 10, 25 = P  
 40 = AM 3, 10 = BN/AM (9" only)

**Type of Static Clogging Indicator** \_\_\_\_\_  
 A, B, BM,  
 C, D, E, ES, J, J4

**Type Code** \_\_\_\_\_  
 1 = Single inlet Connection 2 = Dual Inlets (matching ports only)

**Modification Number (latest version always supplied)** \_\_\_\_\_

**Port Configuration** \_\_\_\_\_  
 0 = G/BSPP Straight Thread Ports  
 3 = NPT Tapered Thread Ports  
 12 = SAE O-Ring Boss Straight Thread Ports  
 16 = SAE Code 61 Flanges

**Seals** \_\_\_\_\_  
 (omit) = Nitrile rubber (NBR) (standard)  
 V = Fluorocarbon elastomer (FKM)

**Bypass Valve** \_\_\_\_\_  
 B1.7 = 25 psid bypass (1.7 bar) B2.7 = 40 psid bypass (2.7 bar) - Standard bypass setting B3.4 = 50 psid bypass (3.4 bar)

**Supplementary Details** \_\_\_\_\_  
 SFREE= Element specially designed to minimize electrostatic charge generation

**Outlet Configuration** \_\_\_\_\_  
 C = Outlet check valve (1/2 psid cracking pressure) DF = Diffuser  
 T = Threaded outlet connection (1 1/2" NPT male) (standard) LI = Lid-mounted Indicator

## Replacement Element Model Code

**5 . 03 . 09 D 03 BN / V**

**Length (nominal inches)** \_\_\_\_\_  
 09, 18, 27

**Type** \_\_\_\_\_  
 D = HF4R (return)

**Filtration Rating (micron)** \_\_\_\_\_  
 3, 5, 10, 20 = BN 3, 10 = BN4AM (9" only)  
 40 = AM 25, 50, 100, 200 = W  
 3, 10, 25 = P

**Element Media** \_\_\_\_\_  
 BN, W, AM, BN4AM, P

**Seals** \_\_\_\_\_  
 (omit) = Nitrile rubber (NBR) (standard)  
 V = Fluorocarbon elastomer (FKM)

**Supplementary Details** \_\_\_\_\_  
 SFREE = (same as above)  
 Element Stacking Interconnector (PN2056730)

## Clogging Indicator Model Code

**VMF 2 C . X / 3 V**

**Indicator Prefix** \_\_\_\_\_  
 VMF = 1/8" NPT Static Indicator  
 VR = G1/2" Static Indicator (lid mount)

**Trip Pressure** \_\_\_\_\_  
**All Other Indicators Gauges E/ES**  
 P = 14.5 psi (1 bar) P = 11.6 psi (0.8 bar)  
 P = 29 psi (2 bar) P = 20 psi (1.4 bar)  
 P = 36 psi (2.5 bar) P = 29 psi (2 bar)

**Type of Indicator** \_\_\_\_\_  
 A = No indicator, plugged port  
 B = Pop-up indicator (auto reset - static only)  
 BM = Pop-up indicator (manual reset)  
 C = Electric switch - SPDT  
 D = Electric switch and LED light - SPDT  
 E/ES = Visual pressure gauge  
 J = Electric switch  
 (Brad Harrison 5-pin mini connector)  
 J4 = Electric switch - M12  
 (Brad Harrison 4-pin micro connector)

**Modification Number** \_\_\_\_\_

**Supplementary Details** \_\_\_\_\_  
 3 = Includes 1/8" NPT Threads

**Seals** \_\_\_\_\_  
 (omit) = Nitrile rubber (NBR) (standard)  
 V = Fluorocarbon elastomer (FKM)


**Light Voltage (D type indicators only)** \_\_\_\_\_  
 L24 = 24V L110 = 110V

(For additional details and options, see Clogging Indicators section.)

Model Codes Containing RED are non-stock items — Minimum quantities may apply — Contact HYDAC for information and availability

# LOW PRESSURE FILTERS

## Dimensions HF4R



Size	09	18	27
Weight (lbs.)	13	17.5	23.2

Dimensions shown are [inches] millimeters for general information and overall envelope size only. Weights listed include element. For complete dimensions please contact HYDAC to request a certified print.

## Sizing Information

Total pressure loss through the filter is as follows:


$$\text{Assembly } \Delta P = \text{Housing } \Delta P + \text{Element } \Delta P$$

### Housing Curve:

Pressure loss through housing is as follows:

$$\text{Housing } \Delta P = \text{Housing Curve } \Delta P \times \frac{\text{Actual Specific Gravity}}{0.86}$$

Adjustments must be made for viscosity & specific gravity of the fluid to be used! (see "Sizing HYDAC Filter Assemblies" in Section B - Overview)



## Element K Factors

$$\Delta P \text{ Elements} = \text{Elements (K) Flow Factor} \times \text{Flow Rate (gpm)} \times \frac{\text{Actual Viscosity (SUS)}}{141 \text{ SUS}} \times \frac{\text{Actual Specific Gravity}}{0.86}$$

(From Tables Below)

Autospec HF4 Depth	5.03.XXDXXBN Low Collapse			
Size	3 μm	5 μm	10 μm	20 μm
5.03.09DXXBN	0.168	0.141	0.079	0.044
5.03.18DXXBN	0.080	0.067	0.038	0.021
5.03.27DXXBN	0.052	0.043	0.024	0.014

Autospec HF4 Paper	5.03.XXDXXP Low Collapse		
Size	3 μm	10 μm	25 μm
5.03.09DXXP	0.250	0.120	0.080
5.03.18DXXP	0.090	0.050	0.030
5.03.27DXXP	0.020	0.010	0.010

Autospec HF4 Water	5.03.09DXXAM & BN/AM		
Size	3 μm	10 μm	40 μm
5.03.09DXXAM	N/A	N/A	0.125
5.03.09DXXBN/AM	0.320	0.230	N/A

Notes: Requires stacking for 18" and 27" configurations.  
Water retention (per 9" section) 500ml at 2 gpm; 150 ml at 20 gpm

Autospec HF4 Wire Mesh	5.03.XXDXXW
Size	25, 50, 100, 200 μm
5.03.09DXXW	0.007
5.03.18DXXW	0.004
5.03.27DXXW	0.002

All Element K Factors in psi / gpm.