



Pump-Transfer Cooler Filtration Unit UF 2-3/UKF 1-3

Operating Data

Ambient temperature	+10 °C to +40 °C							
Volumetric efficiency	>90 % at v = 40 mm²/s							
Mounting position	UKF-1: Optional, but easier to maintain if filter below pump UKF-2 / UKF-3: vertical							
Noise levels	UKF-1: <64 dB(A)	at 1,500 1/m	in					
	Pump [cm3/rev]	1 bar	6 bar					
	15	61	61					
	20	61	61					
	30	61	62					
	40	62	63					
	50	64	66					
	70	67	68					
	100	68	70					
	130	70	72					
	(Test medium: ISO The noise levels are connections, viscos	VG46 at +40 e only a guide ity and reflec) °C) e as the acoustic properties of a roor tions have an effect on the noise lev					
Pump								
Suction pressure across the suction connection	max0.4 bar to 0.9	5 bar						
Operating pressure (oil side)	max. 6 bar							
Medium (oil side)	Mineral oil to DIN 5	1524 Part 1	and Part 2					
Temperature range (oil side)	+10 °C to +80 °C							
Permissible contamination (oil side)	≤NAS12 or ISO440	06: 22/21/18						
Max. viscosity	see viscosity-tempe	erature graph	1					
Drive								
Motor	Three-phase electr Insulation class: F Protection class: IP	ic motor 55						
Speed	1,500 / 1,800 1/min	(50/60 Hz)						
Heat exchanger								
Heat exchanger connections:	Female thread (max The pipes must be of Linear expansion ar must be avoided.	 tightening t connected so od vibrations 	orque 160 Nm) that the connections are stress-free from the pipes to the heat exchange					
Medium (water side):	Water glycol (HWaterOils	FC)						
Temperature range (water side)	+5 °C to +60 °C							
Operating pressure (water side):	max. 30 bar							
Permissible contamination (water side)	The level of particle Particle size <0.6 m Thread-like particles	s in suspensi Im (spherical s cause a rap	on should be less than 10 mg/l.) id increase in pressure losses.					
Water quality	The following ions a phosphate, nitrate, also see table on w	are not corro nitrite, mang ater quality	sive under normal conditions: anese, sodium and potassium					

Symbol

ВM

- **WW**D-

D

(м

General The UKF unit is a compact, easy-to-install system for offline filtration cooling circuits. It consists of a low-noise feed pump, a filter and a plate heat exchanger.

Product Features

Continuous cooling and offline filtration extend the service life of the oil and of the hydraulic system. The offline unit ensures constant oil temperature – regardless of the cycle times of the hydraulic systems. Furthermore, consistent flow rates prevent pressure spikes in the heat exchanger.

Application Field

- Plastic injection moulding machines
- Pressing / Stamping
- Machining centres
- Hydraulic systems
- Gears

Design

There are different versions possible depending on the requirements:

UF - Feed pump with filter

UK – Feed pump with plate heat exchanger

UKF - Feed pump with filter and plate heat exchanger

Offline unit consisting of:

- Low-noise feed pump
- Filter

UKF-1

- Oil-water plate heat exchanger
- The circuit is fitted with check valves to isolate the filter when used with a positive head tank when changing the filter element





Flow rate:	5 – 15 l/min
Motor rating:	0.37 – 0.55 kW
Cooling capacity*:	up to 10 kW







Flow rate:	15 – 60 l/min
Motor rating:	0.75 – 1.5 kW
Cooling capacity*:	up to 30 kW

20 – 200 l/min

1.5 – 4 kW

UKF

UKF-3



Cooling capacity*: up to 90 kW

UF (without heat exchanger)

Dependent on temperature difference and flow rate of the cold and warm medium (see also "Pump-Transfer Cooler Filtration Unit Selection").

Flow rate:

Motor rating:

Water Quality

The following maximum limits are based on a water temperature of +60 °C.

Substances dissolved in water	Concentration (ppm)
pH value	7.0 – 9.0
Electrical conductivity	10 – 500 [μ S/cm]
Cl⁻ (max. 60 °C)	<300
SO4 ⁻²	<50
CaCO ₃	<50
Fe	<0.3
NH ₃	<2
NO ₃	<100
S ⁻²	not suitable
SiO ₂	<30
NH4 ⁺	<0.1
Free chlorine	<0.1
CO3-2	<0.4
H ₂ S	<0.05

Dimensions / Weight

UKF-1

Clearance for filter element removal approx. 50 mm



Weight (unfilled)

Basic unit (motor-pump unit + filter) + heat exchanger

Motor-pump unit	Heat exchanger	
Basic unit: 12 kg	610-10: 3 kg	
	610-20: 5 kg	
	615-10: 6 kg	
	615-20: 8 kg	



Weight (unfilled) Motor-pump unit + heat exchanger + filter

Motor-pump unit	Heat exchanger	Filter
0.75 kW: 16 kg	610-20: 11 kg	MF180: 2 kg
1.5 kW: 20 kg	610-40: 14 kg	LF330: 5 kg
	615-20: 14 kg	LF500: 7 kg
	615-40: 18 kg	







Oil IN

42.9

0

Ţ

UKF-3



Weight (unfilled) Motor-pump unit + heat exchanger + filter

Motor-pump unit	Heat exchanger	Filter
1.5 kW: 44 kg	610-20: 11 kg	MF180: 2 kg
2.2 kW: 48 kg	610-40: 14 kg	LF330: 5 kg
4 kW: 52 kg	610-70: 17 kg	LF500: 7 kg
	610-100: 22 kg	LF660: 8 kg
	610-120: 25 kg	
	615-20: 14 kg	
	615-40: 18 kg	
	615-60: 24 kg	
	615-80: 30 kg	

Model Type

		<u>UKF-2</u> - <u>1.0</u> - <u>P</u> - <u>4</u>	<u>0</u> - <u>1.5</u> - <u>6</u>	<u>510-40</u> - <u>MF180</u> -	<u>10</u> - D
Туре					
UKF =	Pump + heat exchanger + filter				
UF =	Pump + filter				
UK =	Pump + heat exchanger				
Version —					
1.0 =	Heat exchanger series 610				
2.0 =	Heat exchanger series 615				
1.2 / 2.2 =	With filter bypass				
Soals					
P+V =	Static seal Perbunan + Dynamic seal Viton				
P =	Static and dynamic seal Perbunan				
D	*				
Pump now ra					
	cm³/revolution 1,000 1/min 1,500 1/min				
UKF-1	3.5 5 l/min				
	5 7.5 l/min				
	7 10 l/min				
	10 15 l/min				
UKF-2	15 15 l/min 20 l/min				
UKF-2 / UKF -3	20 20 l/min 30 l/min				
	30 30 l/min 45 l/min				
	40 40 l/min 60 l/min				
UKF-3	50 50 l/min 75 l/min				
	60 60 l/min 90 l/min				
	70 70 l/min 105 l/min				
	100 100 l/min 150 l/min				
	130 130 l/min 180 l/min				
Motor					
	0.37 kW/ @ 1.500.1/min				
	0.55 kW @ 1.500 1/min				
	0.75 kW @ 1.500 1/min				
UKF-2 / UKF -3	1 1-6p kW @ 1 000 1/min (6-pole motor)				
	1.5 kW @ 1.500 1/min				
UKF-3	2 2 kW @ 1 500 1/min				
	2 2-6p kW @ 1 000 1/min (6-pole motor)				
	4 kW @ 1.500 1/min				
Plate heat exe	changer – No. of plates				
610	-10 -20 -30 -40 -50 -60 -70 -100 -120				
UKF-1	• •				
UKF-2	• • •				
UKF-3	• • • • • •				
615	-10 -20 -30 -40 -60 -80				
UKF-1	• •				
UKF-2	• • •				
UKF-3	• • • •				
Other plate he	at exchangers on request.				
Filtor					
	NJAW/JW MF160 MF180 LF330 LF500 LF660				
IIKE-2					
0AF-3					
Filtration ratio	ng				
-03 =	3 µm				
-05 =	5 µm				
-10 =	10 µm				
-20 =	20 µm				
For further det	ails on filter elements, see relevant brochure in Flui	d Filters catalogue			
Differential n	ressure of clogging indicator				
D =	visual-electrical				
Additional cloc	aging indicators on request, see relevant brochure in	Fluid Filters catalogue			

Pump-Transfer Cooler Filtration Unit Selection

Determining the cooling capacity

Estimating the cooling capacity requirements for mineral oil based on increase in tank temperature

$$p = \frac{\Delta T \times V}{t} \times \frac{1}{35}$$

p = heat dissipation [kW]

- ΔT = temperature increase in the reservoir [K]
- V = tank capacity [I]
- T = operating time [min]

Example:

In an system, the tank temperature rises from +20 °C to +70 °C (= 50 K) in 30 minutes. The tank volume is 100 l.

$$p = \frac{50 \times 100}{30} \times \frac{1}{35}$$

$$p = 4.8 [kW]$$

Estimating the cooling capacity requirement based on installed electrical power

 $p \approx \frac{1}{4} x$ installed electrical power Calculating the oil and water outlet temperature

Drop in oil temperature:

$$\Delta T \approx \frac{p}{Q_{oii}} \times 36$$

Increase in water temperature:

$$\Delta T \approx \frac{p}{Q_{Water}} \times 14.4$$

Cooling capacity [kW]

р

Oil flow rate [l/min]Water flow rate [l/min]

Selection of the plate heat exchanger:

A sizing program is available to calculate accurately the required cooling capacity and a suitable plate heat exchanger. For this, five of the following seven variables are required:

- Oil inlet and outlet temperature
- Oil flow rate
- Water inlet and outlet temperature
- Water flow rate
- Cooling capacity
- Additionally, the viscosity of the oil is required.

The following graphs show the selection of plate heat exchangers based on cooling capacity.

Operating condition: $T_{oil} = +55 \text{ °C}$; oil ISO VG 46; $\frac{Q_{oil}}{Q_{Water}} = 1$







Operating condition: T_{oii} = +55 °C; oil ISO VG 46; $\frac{Q_{oii}}{Q_{Water}}$ = 4







Operating condition: $T_{oil} = +55 \text{ °C}$; oil ISO VG 46; $\frac{Q_{oil}}{Q_{Water}} = 4$







Viscosity

Viscosity / temperature graph to DIN 51519 Viscosity index 50

Viscosity / temperature graph Viscosity index 0 to 200 oil ISO VG 320





To DIN 51519, viscosity index 50, Temperature of medium (oil) +10 °C to +80 °C; short-term operation at higher viscosities (cold start) is permitted. The viscosity index indicates how much the viscosity of the oil changes with temperature.

It is a measure of the temperature properties of different oils. The higher the viscosity index of an oil, the smaller the change in viscosity in relation to the temperature.

Graphs for Motor-pump Selection















16 **HYDAC**

Filter Selection

Cleanliness requirements for lubricating and hydraulic components. The cleanliness level required in lubricating and hydraulic systems is determined by the most sensitive component.

Type of system/Area of application/	Recommended	
Components	cleanliness class	
Systems with servo hydraulics sensitive to fine contamination	15/13/10	
Industrial hydraulics	17/15/12	
Proportional technology		
 High pressure systems 		
Industrial and mobile hydraulics		
 Electromagnetic control valve technology 	18/15/12	
 Medium pressure and low pressure systems 	19/16/14	
Industrial and mobile hydraulics with low	20/18/15	
demands on wear protection		
Forced-feed circulatory lubrication on gears	18/16/13	
New oil	21/19/16	
Pumps/Motors		
Axial piston pump	18/16/13	
 Radial piston pump 	19/17/13	
Gear pump	20/18/15	
Vane pump	19/17/14	
Valves		
Directional valves	20/18/15	
 Pressure control valves 	19/17/14	
 Flow valves 	19/17/14	
Check valves	20/18/15	
 Proportional valves 	18/16/13	
Servo valves	16/14/11	
Cylinders	20/18/15	

Depending on the conditions of the system and the environment, filters with the same filtration rating perform differently. Typical fluid cleanliness classes achieved with HYDAC elements are shown below:

	25											19/1	/13 – 22/19/16	
х	20										18/1	5/12 – 21/	18/15	
atin	15									17/14	4/11 – 20/1	17/14		
on r 200)	10								15/12/9 -	- 19/16/13	19/16/13			
trati ₀ ≥ :	5 12/S					2/9/6 – 17/14/11								
Filt (β _{×(}	3		10/	7/4 – 13/1	0/7									
		10/7/4	11/8	/5 12/	9/6 13/1	0/7 14/1	1/8 15/	12/9 16/1	3/10 17/1	4/11 18/1	5/12 19/1	16/13 20/1	7/14 21/	18/15 22/19/

Oil cleanliness to ISO 4406

Notes

On piping

The pressure differential in a hydraulic line is dependent on:

- Flow rate
- Kinematic viscosity
- Pipe dimensions and can be estimated for hydraulic oils as follows:

$$\Delta p[bar] = 5.84 x \frac{I[m]}{d^4} x Q$$

- = Pipe length [m] L
- d = Internal diameter of pipe [mm]
- Q = Flow rate [l/min]
- = Kinematic viscosity [mm²/s] n

This applies to straight pipe runs and

hydraulic oils, and to laminar flow.

Additional threaded connections and pipe bends increase the pressure differential.

Notice

- As few threaded connections as possible
- Few pipe bends; if unavoidable, use large radius
- Difference in height between pump and oil level as small as possible
- Hoses must be suitable for a vacuum of min. 5,000 mmW
- Do not reduce pipe cross-section predetermined by the unit

Note

The information in this brochure relates to the operating conditions and applications described. For applications and operating conditions not described, please contact the relevant technical department. Subject to technical modifications.

(HYDAC)

HYDAC COOLING GMBH



INTERNATIONAL

Industriegebiet 66280 Sulzbach/Saar Germany

Tel.: +49 6897 509-01 Fax: +49 6897 509-454

E-mail: cooling@hydac.com Internet: www.hydac.com