


**Basics of electronics  
and measurement  
technology**

01001101  
01001111  
01010011  
01010011  
01001101  
01000001  
01001110  
01001110  
00101110  
01000101  
01010101

HTC



## Basics of electronics and measurement technology

Publisher HYDAC Service GmbH  
Training Center  
Hirschbachstrasse 2  
D-66125 Dudweiler/Saar  
E-Mail: Training-Center@hydac.com  
SAP No. 3802481

Illustrations Insofar as a differing reference source has not been noted: HYDAC International GmbH

© 2012 by HYDAC International GmbH  
All rights reserved.

[www.hydac.com](http://www.hydac.com)

#### **Exclusion of liability**

We have made every effort possible to ensure the accuracy of the content in this document. Nevertheless, errors cannot be entirely excluded. For this reason, we assume no liability for errors and deficiencies in the document nor for any consequential damage that may result. The information contained in this document will be checked on a regular basis and any necessary corrections will be contained in following editions. We are grateful for any recommendations or suggestions for improvement. We reserve the right to make changes to the content in this document without prior notice. Reprinting is possible only with our permission!

# I Introduction to Physical Principles

<b>1</b>	<b>Introduction</b>	9
1.1	Basic SI quantities and units	9
1.2	Unit prefixes	10
<b>2</b>	<b>Fundamental quantities and laws</b>	11
2.1	DC circuit	11
2.2	Electrical charge, elementary charge	12
2.3	Electrical current	12
2.4	Voltage and potential	13
2.5	Current and voltage types	14
2.6	Root mean square	15
2.7	Ohm's law	16
2.8	Resistance and conductance	17
2.9	Temperature interdependence of fixed resistors	19
2.10	Temperature interdependence of NTC/PTC resistors	20
2.11	Performance and energy	21
2.12	Efficiency	22
<b>3</b>	<b>Electrical and magnetic fields</b>	23
3.1	Electrostatic field	23
3.2	Magnetism	24
3.3	Magnetic field	25
3.4	Electromagnetism	26
3.5	Induction	27
<b>4</b>	<b>Semiconductor physics</b>	29
4.1	Semiconductor materials	29
4.2	Specific resistance/conductivity	30
4.3	Doping	31

# II Components and their application

<b>1</b>	<b>Introduction</b>	35
1.1	Safety information	35
1.2	Basic information on circuits	36
<b>2</b>	<b>Voltage and current sources</b>	37
2.1	Ideal voltage source	37
2.2	Real voltage source	38
2.3	Ideal current source	39
2.4	Real current source	40
2.5	Voltage generation and energy conversion	41
2.5.1	Generator (dynamo)	42
2.5.2	Voltaic cell	43
<b>3</b>	<b>Fixed resistor</b>	45
3.1	General	45
3.2	Series control of resistors	46
3.3	Parallel control of resistors	46
3.4	Measuring current and voltage in resistor	47
<b>4</b>	<b>Capacity (capacitor)</b>	49
4.1	General	49
4.2	Series control of capacities	50
4.3	Parallel control of capacities	50
4.4	Series control of R and C at voltage source	51
<b>5</b>	<b>Inductance (solenoid coil)</b>	53
5.1	General	53
5.2	Series control of inductors	54
5.3	Parallel control of inductors	54
4.4	Series control of R and L at voltage source	55
5.5	Deactivating oHM <sub>Gc</sub> -inductive load without flyback diode	56
5.6	Deactivating oHM <sub>Gc</sub> -inductive load with flyback diode	57
5.7	Electromagnet	58
<b>6</b>	<b>Semiconductor diode</b>	59
1.1	General	59
6.2	Diode performance	60
6.3	Half-cycle rectifier circuit (E1)	61
6.4	Bridge rectifier circuit (B2)	62
6.5	Smoothing and filtering	63

<b>7</b>	<b>Bipolar transistor</b>	65
7.1	General	65
7.2	Basic circuits	67
7.3	Transistor as switch	68

### III Measuring transducers

<b>1</b>	<b>Introduction</b>	73
1.1	Overview	73
1.1	Basic remarks about measuring	73
1.3	Measured variables in hydraulics	74
<b>2</b>	<b>Design</b>	75
2.1	Sensor cell	76
2.1.1	Strain gauges	77
2.1.1.1	Strain gauge variants	78
2.1.1.2	Strain gauge measuring bridge	79
2.1.2	Piezoelectric	80
2.1.3	Thermocouple element	81
2.1.4	Inductive (inductive proximity switch)	82
2.1.5	Capacitive (capacitive proximity switch)	83
2.2	Signal processing	84
2.3	Electrical interface	85
2.4	Measurement range	86

### IV Measuring process

<b>1</b>	<b>Introduction</b>	89
1.1	Measurement chain	89
1.2	Selecting measuring transducer	90
1.2.1	Accuracy	91
1.2.2	Performance deviation at maximum setting	92
1.2.3	Performance deviation at minimum setting	93
1.2.4	Accuracy indication: typ. and max.	94
1.2.5	Electromagnetic compatibility (EMC)	95
1.2.6	Temperature impact	96
1.2.7	Measuring dynamics	97
1.2.8	Long-term stability	98
1.3	Selecting measuring instrument	99
1.3.1	Sampling rate	100
1.3.2	Transient recorder with trigger	101
1.3.3	Measurement channel	102
<b>2</b>	<b>Pressure measurement equipment</b>	103
2.1.	Introduction	103
2.2	Mechanical pressure transducer	104
2.2.2	Pressure transducer with diaphragm	105
2.2.1	Pressure transducer with bourdon tube	106
2.2.4	Plunger pressure gauge	107
2.2.3	Differential pressure transducer	108
2.2.5	Calibration	109
2.3	Electronic pressure transducer	110
2.3.1	Strain gauges	111
2.3.2	Piezoresistive	112
2.3.3	Capacitive	113
2.3.4	Accuracy	114
2.4	Pressure switch	115
2.4.1	Designs	116
2.4.1.1	Mechanical pressure switch	117
2.4.1.2	Electrical pressure switch	118
2.4.2	Accuracy	119
<b>3</b>	<b>Volume flow measurement equipment</b>	121
3.1.	Introduction	121
3.2	Displacement principle	122
3.2.1	Gear wheel meter	122
3.2.2	Oval wheel meter	123
3.3	Flow principle	124
3.3.1	Volume flow orifice	124
3.3.2	Floater method	125
3.3.2.1	Gravity floater	125
3.3.2.2	Spring floater	126
3.3.3	Turbine rotor sensor	127

3.4	Speed measurement	128
3.4.1	Ultrasonic sensor	128
3.4.2	Calorimetric measurement	129
<b>4</b>	<b>Temperature measurement equipment</b>	<b>131</b>
4.1	Resistance thermometer	132
4.2	Thermistors	133
4.3	Thermocouple element	134
4.4	Pyrometer	135
4.5	Comparison	136
4.6	Accuracy	137
4.7	Response	138
4.8	Installation criteria	139
<b>5</b>	<b>Level measurement equipment</b>	<b>141</b>
5.1	View glass	142
5.2	View glass with float switch	143
5.3	View glass with temperature switch	144
5.4	Capacitive measuring method	145
<b>6</b>	<b>HMG 3000</b>	<b>147</b>
6.1	Tasks and functions	147
6.2	Technical data	148
6.3	Device	149
6.3.1	Operating element	149
6.3.2	Ports	150
6.4	Performing a measurement	151
6.4.1	Setting measurement channels	151
6.4.2	Display settings	152
6.4.3	Starting a recording	153
6.4.4	Viewing recordings	154
6.5	HMGWIN 3000	155
<b>V</b>	<b>Annex</b>	
<b>1</b>	<b>Tables</b>	<b>157</b>
1.1	Electrical engineering units	157
1.2	Physical constants	158
1.3	Greek symbols for formulas	158
1.4	Color code for labeling 4-ring resistors	159
1.5	Color code for labeling 5-ring resistors	160
<b>2</b>	<b>Formulary</b>	<b>161</b>
2.1	Basic variables	161
2.2	Resistive circuit	162
2.3	Electric field and capacitor	163
2.4	Magnetic field and solenoid coil	164
<b>3</b>	<b>Symbols</b>	<b>165</b>
3.1	Basic electronic symbols	165
3.2	Other electronic symbols	166
<b>4</b>	<b>Protective measures</b>	<b>167</b>
4.1	General	167
4.2	Electrocution	168
4.3	Standards	169
4.4	Protection ratings	169
4.5	Protection classes	170



## Preface

HYDAC is an internationally-active company with a wide product pallet concerning fluid technology. The range of products extends from components through subsystems right up to complex, controlled and regulated drive units for mobile and stationary machines and systems.

In addition, we offer our customers a comprehensive package of technical services within the scope of HYDAC fluid engineering for media such as hydraulic oils, lubricants, cooling lubricants and water.

Our aims are exclusively to increase the availability of machines and systems and to lower the operating costs for our customers.

HYDAC has a worldwide competence network as well as high quality demands and customer orientation. and thus fulfils the high requirements placed on them by the international market.

The continual expansion of our global presences with strong local orientation makes it possible for us to attend to the needs of our customers at nearly any location in the world.

HYDAC is always close at hand with 12 Sales Offices in Germany, over 45 foreign subsidiaries, partially with their own Production or Assembly Departments, more than 500 Sales and Service Partners and over 7000 employees.

In order to ensure that our employees, service partners and customers remain capable of fulfilling the consistently increasing demands of their vocational environments, we provide training courses, seminars and practical training in our Training Center.

Here the term "Lifelong learning" is beginning to gain more and more importance.

Learning does not stop once you have finished school, training or studies, as learning is the most important tool for development, and therefore for the creation of individual chances in work and in life in general.

Lifelong learning breaks through the barriers of standard educational structures and the division into the strictly sequential sections of educational development, which is often concluded with school or further education qualifications. This also comprises of recognizing and utilizing education as a path to increased personal responsibility in your lives. Competency in lifelong learning will in future become a more and more important key for personal, economic and social success.

In order to adapt this innovative form of learning to individuals, we have decided on a learning concept which combines e-learning media with the advantages of classroom training sessions and practical training according to requirements.

This concept also includes the development of a series of books in which both basic hydraulics topics as well as more advanced hydraulic system topics are to be addressed.

This book can be utilized analog to our seminars and training courses and should at the same time serve as a reference book for further vocational practice.

Jürgen Ringle  
Head of HYDAC Training Center

# I Introduction to Physical Principles

This chapter explains the physical principles and effects of electrical engineering. It will focus in particular on the basic physical quantities and their units.





Notes:

# 1 Introduction

## 1.1 Basic SI quantities and units

Physical quantities are measurable characteristics of bodies or physical states. They consist of a numerical value and the unit of measure. Only SI units or units derived therefrom are used in technology (see table).

**SI units:**

<b>Basic quantity</b>	<b>Basic unit</b>	<b>Unit symbol</b>	<b>Symbol</b>
Length	Meter	m	l
Mass	Kilogram	kg	m
Time	Second	s	t
Electrical current	Ampere	A	l
Temperature	Kelvin	K	T
Quantity of material	Mol	mol	n
Light intensity	Candela	cd	l <sub>v</sub>

Fig. Table of SI units

## 1.2 Unit prefixes

Very large and very small quantity values are expressed with a unit prefix.

The unit prefixes (a.k.a. SI prefixes) are based on orders of magnitude with whole number exponents and are used in the International System of Units (SI).

The SI prefixes are defined as follows:

SI prefixes	Name	Value	
T	Tera	$(10^3)^4 = 10^{12}$	1,000,000,000,000
G	Giga	$(10^3)^3 = 10^9$	1,000,000,000
M	Mega	$(10^3)^2 = 10^6$	1,000,000
k	Kilo	$(10^3)^1 = 10^3$	1,000
h	Hecto	$10^2$	100
da	Deca	$10^1$	10
Unit		$10^0$	1
D	Deci	$10^{-1}$	0.1
c	Centi	$10^{-2}$	0.01
m	Milli	$(10^{-3})^1 = 10^{-3}$	0.001
$\mu$	Micro	$(10^{-3})^2 = 10^{-6}$	0.00.001
n	Nano	$(10^{-3})^3 = 10^{-9}$	0.00.000.001
p	Piko	$(10^{-3})^4 = 10^{-12}$	0.00.000.000.001
f	Femto	$(10^{-3})^5 = 10^{-15}$	0.00.000.000.000.001

## 2 Fundamental quantities and laws

### 2.1 DC circuit

A circuit consists of at least:

- A power generator (e.g. battery, generator)
- A consumer (e.g. bulb, motor)
- Go and return lines




Fig. Graphic of DC circuit




Fig. Symbolic view of DC circuit

## 2.2 Electrical charge, elementary charge

Symbol	Basic unit
$Q$	$C = As$ (Coulomb)

All electrical phenomena can be attributed to a charge. A distinction is made between a positive (+) and negative (-) charge. There is electrostatic interaction between electrical charges (Coulomb's law). Charges with the same sign repel each other. Charges with opposite signs attract each other.

In physical terms, each charge quantity is an integral multiple of the elementary charge  $e$  ( $e = +/- 1.602 \cdot 10^{-19} C$ ). Electrons carry a negative elementary charge, protons carry a positive elementary charge. A deficit of electrons in matter causes the matter to have a positive charge, an excess of electrons causes it to have a negative charge.




Fig. Attraction and repulsion of electrical charges



**Note:**

Work is needed to disconnect two charge carriers with different polarities.  
 Work = force • path  $\Rightarrow W = F \cdot s$

## 2.3 Electrical current

Symbol	Basic unit
$I$	$A$ (Ampere)

The directed motion of the electrical charge carrier is referred to as electrical current. Electrical current only flows when there are enough free and moveable charge carriers between two different electrical charges. One example is in a conductive material (metal, liquid, etc.).

**Example:**

The current flow can be equated to flowing water in a tube. The more water in the tube, the more water comes out of the end of the tube. This is the same with electrical current.




Fig. Comparison of water flow and electrical current

The more free charge carriers available, the greater the intensity of the electrical current through the conductor. In metallic conductors, electrons are the charge carriers.



### Open and closed circuit:

In general, charges always move in a circuit. That means the current always flows in a closed cycle. Thus if the switch is open, no current can flow. Only when the switch is closed can current flow, since the circuit is closed.




Fig. Circuit diagram for electrical circuit

## 2.4 Voltage and potential

Voltage symbol	Basic unit for voltage
$U$	$V$ (Volt)

**Electrical voltage is the difference in charges between two poles.**

Voltage sources have at least two poles with different charges. One pole is positive with a deficit of electrons. The other pole is negative with an excess of electrons. The difference in the amount of electrons is referred to as electrical voltage. When the poles of the voltage source are connected to each other, current flow is created (discharge). Here the current always flows from the voltage source's positive pole to its negative pole (technical direction of current). Electrical voltage is thus the driving force that causes charge motion.




Fig. Battery voltage



#### Note:

Voltage arises from separation of charge. The tendency to re-equalize separated charges is electrical voltage, with the symbol  $U$ . Voltage is the work toward separation per charge.

Potential symbol	Basic unit for potential
$\varphi$ (Phi)	V (Volt)

The potential  $\varphi$  of a point is equal to the voltage in comparison to a specific reference point (e.g. mass  $\varphi_0 = 0$  V).

When measuring a positive value, the potential is more positive than the reference point and the prefix is positive ( $\varphi_2, \varphi_3$ ). When measuring a negative value, it is the opposite ( $\varphi_1$ ).

In a circuit diagram, the voltage's direction of operation is shown by an arrow. In general, the voltage arrow is from positive to negative or from a higher voltage value (potential) to a lower voltage value (potential).




Fig. Battery potential

## 2.5 Current and voltage types

### Direct current (DC):

Direct current is a current that flows with the same strength in the same direction (polarity). Typical DC sources are batteries, solar cells and fuel cells. DC technology is used e.g. in amplifiers or circuits with semiconductor elements and relays.

### Alternating current (AC):

Alternating current is a current that periodically alters its quantity and direction (polarity). Since AC is more operationally efficient than DC, our power supply is run on sinusoidal alternating current. Another application area is telecommunications engineering.

### Undulatory current:

Undulatory current is a current in which portions of DC and AC overlap. Undulatory current is used in modulation, AC amplification and telephone networks.




Fig. DC performance




Fig. AC performance




Fig. Pulsating current performance



**Note:**

All other physical views are based on a DC source.

## 2.6 Root mean square

The root mean square  $U_{eff}$  is the root mean square of a signal changing over time.

It corresponds to the value of a DC voltage that converts the same energy in an oHMGc consumer in the same amount of time. Its quantity depends on the peak value  $\hat{U}$  (amplitude) and wave form of the signal.

Most often the root mean square voltage is given in the AC voltage that can be drawn from the power grid. This sinusoidal voltage, with a frequency of 50 Hz (60 Hz in the United States and other countries) and a peak value of 325 V, delivers the same output to a consumer (e.g. a toaster) as a DC voltage of 230 V in the average amount of time. However, peak output at peak value time is double.

Using the root mean square from the periodic current and voltage paths, the laws of direct current can be applied to oHMGc consumers instead of those of alternating current. The root mean square of a sinusoidal AC voltage is calculated using the following formula.

**Formula:**

$$U_{eff} = U = \frac{\hat{U}}{\sqrt{2}}$$




Fig. Root mean square performance



**Note:**

$U_{eff}$  = root mean square

$U$  = DC voltage

$\hat{U}$  = peak value of AC voltage

$U_{ss}$  = Top peak value of AC voltage



Broch.: Accumulators DEF 3,000



Brochure: Filter Range DEF 7,000



Broch.: Process Technology DEF 7,700



Brochure: Fluid Service DEF 7,929



Broch.: Compact Hydraulics DEF 5,300



Brochure: Accessories DEF 6,100



Brochure: Electronics DEF 18,000



Brochure: Cooling Systems DEF 5,700

# Global presence. Local expertise. [www.hydac.com](http://www.hydac.com)



- HYDAC Headquarters
- HYDAC Companies
- HYDAC Distributors and Service Partners

# Local expertise

## HYDAC INTERNATIONAL


**HYDAC Service GmbH  
TRAINING CENTER**

Hirschbachstraße 2  
66125 Dudweiler/Saar  
Germany

Phone:  
+49 (0) 68 97 / 509 - 1022

Fax:  
+49 (0) 68 97 / 509 - 1014

Internet: [www.hydac.com](http://www.hydac.com)  
E-Mail: [Training-Center@hydac.com](mailto:Training-Center@hydac.com)



3802481